





THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	WEIGHT
SEE SHEET 2	SEE SHEET 2



SPECIFICATION:

1. STANDARD:
 UNIT TYPE: MONITORED SWITCHED
 ORIENTATION: VERTICAL, 0U FULL
 OUTLET QTY & TYPE: (30)C13, (6)C19
 INPUT VOLTAGE: 100-120/200-240VAC
 INPUT CURRENT: 30A (24A DERATED)
 BREAKER QTY & TYPE: (3) 20AMP, DOUBLE-POLE
 INPUT PHASE: THREE-PHASE, WYE
 RATED POWER: 8.6 KVA
 INPUT PLUG: NEMA L21-30P
 INPUT POWER CORD: SEE SHEET 2 FOR PART NUMBER TABLE
 REGULATORY STANDARD: RoHS COMPLIANT



2. ADDITIONAL:
 THE G6 CONTROLLER IS NOT BACKWARDS COMPATIBLE WITH ANY LEGACY CONTROLLERS

3. ACCESSORIES:
 DOCUMENTATION KIT
 PRODUCT SAFETY WARNING SHEET

NOTES:

- PRIMARY DIMENSIONS ARE IN MILLIMETERS. SECONDARY DIMENSION ARE IN [INCHES]
- INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE, AND LOCAL CODES
- VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART
- FOR FULL PRODUCT FUNCTIONALITY REFER TO USER MANUAL
- DRAWING VIEWS SHOW THE INPUT CORD IN THE "TOP END FED" CONFIGURATION

IDENTIFICATION
 FOR FINISHED GOOD PART NUMBER & DESCRIPTION TABLE SEE SHEET 2 CONFIGURABLE PART NUMBERS: P36E35G-XX Y Z



REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
00A	08/31/2023	CCQ	CSH	MJD	INITIAL RELEASE	P36E35G-XXYZ

WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGN THE CLIENT SIGNATURE BOX. THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY.

SIGN _____ DATE _____ PRINT _____

TITLE: INTELLIGENT SERIES PDU
P36E35G-XXYZ
CUSTOMER DRAWING

ITEM REVISION NAME: _____

DATASHEET FILE NAME: _____

UNLESS OTHERWISE SPECIFIED DIMENSIONAL TOLERANCE ARE: mm [IN]

Tolerance(mm)	0<L<50	±0.5
	50<L<250	±1.0
	250<L<500	±1.5
	500<L<1000	±2.5
	1000<L<2000	±4.0

MATERIAL/COLOR: N/A

DRAWING NUMBER: P36E35G-XXYZ_DC

THIRD ANGLE PROJECTION

DRAWN BY	DATE	CHK	SCALE
CCQ	08/31/2023	CSH	NONE

SHT 1 OF 2 SCALE: B

2



1

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

FINISHED GOOD PART NUMBER	FINISHED GOOD DESCRIPTION	COLOR	INPUT CORD LENGTH	WEIGHT
P36E35G	G6 MS PDU, 30AMP, (30)C13 (6)C19, NEMA L21-30P-3M, TOP FED, BLACK	BLACK (RAL 9005)	3M(+254MM/-127MM) 10' [+10"/-5"]	8.3kg

B

B



A

A

WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGN THE CLIENT SIGNATURE BOX. THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY		SIGN
		DATE
		PRINT
TITLE INTELLIGENT SERIES PDU P36E35G-XYZ CUSTOMER DRAWING		
ITEM REVISION NAME		PANDUIT
DATASHEET FILE NAME:		
UNLESS OTHERWISE SPECIFIED DIMENSIONAL TOLERANCE ARE: mm [IN]		MATERIAL/COLOR: N/A
THIRD ANGLE PROJECTION Tolerance(mm) 0<math>0<math>50<math>250<math>500<math>1000<math>2000 ±0.5 ±1.0 ±1.5 ±2.5 ±4.0		DRAWING NUMBER: P36E35G-XYZ_DC
DRAWN BY	DATE	SCALE
CCQ	08/31/2023	NONE
CHK	CSH	
SHT 2 OF 2		SCALE B

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
00A	08/31/2023	CCQ	CSH	MJD	INITIAL RELEASE	P36E35G-XYZ

2



1