




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	WEIGHT
SEE SHEET 2	SEE SHEET 2




DRAWING VIEWS SHOW THE INPUT CORD IN THE "TOP END FED" CONFIGURATION  
PARTS USING UPGRADABLE IPDU BLANKING PANEL CAN BE UPGRADED TO INTELLIGENT MODELS USING PANDUIT CONTROLLER PART NUMBER MA002



- SPECIFICATION:**
- STANDARD:
    - UNIT TYPE: SEE SHEET 2
    - ORIENTATION: VERTICAL, 0U FULL
    - OUTLET QTY & TYPE: (32) C13, (6) C19
    - INPUT VOLTAGE: 200-240VAC
    - INPUT CURRENT: 30A (24A DERATED)
    - BREAKER QTY & TYPE: (2) 20AMP, DOUBLE-POLE
    - INPUT PHASE: SINGLE-PHASE
    - RATED POWER: 5.0 kVA
    - INPUT PLUG: NEMA L6-30P
    - INPUT POWER CORD: SEE SHEET 2 FOR PART NUMBER TABLE
    - REGULATORY STANDARD: RoHS COMPLIANT
  - ADDITIONAL:
    - THE G6 CONTROLLER IS NOT BACKWARDS COMPATIBLE WITH ANY LEGACY CONTROLLERS
  - ACCESSORIES:
    - DOCUMENTATION KIT
    - PRODUCT SAFETY WARNING SHEET

- NOTES:**
- PRIMARY DIMENSIONS ARE IN MILLIMETERS. SECONDARY DIMENSION ARE IN [ INCHES ]
  - INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE, AND LOCAL CODES
  - VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART
  - FOR FULL PRODUCT FUNCTIONALITY REFER TO USER MANUAL
  - DRAWING VIEWS SHOW THE INPUT CORD IN THE "TOP END FED" CONFIGURATION
  - PARTS USING UPGRADABLE IPDU BLANKING PANEL CAN BE UPGRADED TO INTELLIGENT MODELS USING PANDUIT CONTROLLER PART NUMBER MA002


**IDENTIFICATION**  
FOR FINISHED GOOD PART NUMBER & DESCRIPTION TABLE SEE SHEET 2 CONFIGURABLE PART NUMBERS: **P38D25G-XX Y Z**



**BOTTOM VIEW**

WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGN THE CLIENT SIGNATURE BOX. THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY.

TITLE <b>INTELLIGENT SERIES PDU P38D25G-XXYZ</b> CUSTOMER DRAWING		SIGN	
ITEM REVISION NAME		DATE	
DATASHEET FILE NAME:		PRINT	
UNLESS OTHERWISE SPECIFIED DIMENSIONAL TOLERANCE ARE: mm [IN]		MATERIAL/COLOR: N/A	
Tolerance(mm) 0.4<50 ±0.5 0.4<250 ±1.0 250.4<500 ±1.5 500.4<1000 ±2.5 1000.4<2000 ±4.0		DRAWING NUMBER: <b>P38D25G-XXYZ_DC</b>	
THIRD ANGLE PROJECTION	DRAWN BY: CCQ	DATE: 09/04/2023	SCALE: NONE
	CHK: CSH		SCALE: SHT 1 OF 2
			SCALE: B



**PLUG/RECEPTACLE BLOCK**

**PLUG**  
NEMA L6-30P, 2P 3W  
30A, 250V MAX RATED INPUT  
24A DERATED

**RECEPTACLES**  
IEC 60320/C19  
16A, 250V MAX RATED OUTPUT

**RECEPTACLES**  
IEC 60320/C13  
10A, 250V MAX RATED OUTPUT

00A	09/04/2023	CCQ	CSH	MJD	INITIAL RELEASE	P38D25G-XXYZ
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN

