

2



1

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

FINISHED GOOD PART NUMBER	FINISHED GOOD DESCRIPTION	COLOR	INPUT CORD LENGTH	WEIGHT
P36E12G	G6 MS PDU, 50AMP, (30) C13 (6) C19, CS8365-3M, TOP FED, BLACK	BLACK (RAL 9005)	3M(+254MM-127MM) 10'[+10"/-5"]	10.2kg

B

B

A

A

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
00A	09/21/2023	NW	CSH	MJD	INITIAL RELEASE	P36E12G-XYZ

WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGN THE CLIENT SIGNATURE BOX. THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY	SIGN	
	DATE	
	PRINT	
TITLE		INTELLIGENT SERIES PDU P36E12G-XYZ CUSTOMER DRAWING
ITEM REVISION NAME:		
DATASHEET FILE NAME:		
UNLESS OTHERWISE SPECIFIED DIMENSIONAL TOLERANCE ARE: mm [IN]		PANDUIT MATERIAL/COLOR: N/A
THIRD ANGLE PROJECTION		
Tolerance(mm) 0<L<50 ±0.5 50<L<250 ±1.0 250<L<500 ±1.5 500<L<1000 ±2.5 1000<L<2000 ±4.0		DRAWING NUMBER: P36E12G-XYZ_DC
DRAWN BY	DATE	SCALE
NW	09/21/2023	NONE
CHK		SCALE
CSH		B
SHT 2 OF 2		

2



1