




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



LEFT VIEW




REAR VIEW



RIGHT VIEW

FOR LENGTH SEE SHEET 2 PART NUMBER TABLE.



FRONT VIEW

1

PANDUIT P/N	WEIGHT
P24D01G-XXYZ	SEE SHEET 2

SPECIFICATION:


1. STANDARD:
- |                      |                                   |
|----------------------|-----------------------------------|
| UNIT TYPE:           | MONITORED INPUT                   |
| ORIENTATION:         | VERTICAL, MID                     |
| OUTLET QTY&TYPE:     | (18) C13, (6) C19                 |
| INPUT VOLTAGE:       | 100-120/200-240VAC                |
| INPUT CURRENT:       | 30A (24A DERATED)                 |
| BREAKER QTY&TYPE:    | (3) 20A, DOUBLE-POLE              |
| INPUT PHASE:         | THREE-PHASE WYE                   |
| RATED POWER:         | 8.6KVA                            |
| INPUT PLUG:          | NEMA L21-30P                      |
| INPUT POWER CORD:    | SEE SHEET 2 FOR PART NUMBER TABLE |
| REGULATORY STANDARD: | RoHS COMPLIANT                    |
2. ADDITIONAL:  
THE G6 CONTROLLER IS NOT BACKWARDS COMPATIBLE WITH ANY LEGACY CONTROLLERS
3. ACCESSORIES:  
DOCUMENTATION KIT  
PRODUCT SAFETY WARNING SHEET

NOTES:

- PRIMARY DIMENSIONS ARE IN MILLIMETERS. SECONDARY DIMENSION ARE IN [ INCHES ]
- INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE, AND LOCAL CODES
- VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART
- FOR FULL PRODUCT FUNCTIONALITY REFER TO USER MANUAL
- DRAWING VIEWS SHOW THE INPUT CORD IN THE "TOP END FED" CONFIGURATION
- OUTLETS ARE WIRED LINE TO LINE (208V)

IDENTIFICATION

FOR FINISHED GOOD PART NUMBER & DESCRIPTION TABLE SEE SHEET 2 CONFIGURABLE PART NUMBERS: P24D01G-XX Y Z



BOTTOM VIEW

**PLUG/RECEPTACLE BLOCK**

	PLUG NEMA L21-30P, 4P 5W 30A, 120/208V MAX RATED INPUT 24A DERATED
	RECEPTACLES IEC 60320/C19 16A, 250V MAX RATED OUTPUT
	RECEPTACLES IEC 60320/C13 10A, 250V MAX RATED OUTPUT

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
00A	10/11/2023	LWB	CSH	MJD	INITIAL RELEASE	P24D01G-XXYZ

WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGN THE CLIENT SIGNATURE BOX. THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY.

TITLE	BASIC SERIES PDU P24D01G-XXYZ CUSTOMER DRAWING	
ITEM REVISION NAME		
DATASHEET FILE NAME:		
UNLESS OTHERWISE SPECIFIED DIMENSIONAL TOLERANCE ARE: mm [IN]	MATERIAL/COLOR: N/A	
THIRD ANGLE PROJECTION	DRAWING NUMBER: P24D01G-XXYZ_DC	
DRAWN BY: LWB	DATE: 10/11/2023	SCALE: NONE
CHK: SEAN	SCALE: NONE	SHT 1 OF 2
		SCALE: B

2

2

1

2



1

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

FINISHED GOOD PART NUMBER	FINISHED GOOD DESCRIPTION	COLOR	INPUT CORD LENGTH	WEIGHT
P24D01G	G6 MI PDU,30AMP,(18) C13,(6) C19,NEMA L21-30P-3M , TOP FED, BLACK	BLACK (RAL 9005)	3M(+254MM-127MM) 10' [+10"/-5"]	7.9kg

B

B



A

A

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
00A	10/11/2023	LWB	CSH	MJD	INITIAL RELEASE	P24D01G-XXYZ

WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGN THE CLIENT SIGNATURE BOX. THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY		SIGN
		DATE
		PRINT
TITLE BASIC SERIES PDU P24D01G-XXYZ CUSTOMER DRAWING		
ITEM REVISION NAME		<b>PANDUIT</b>
DATASHEET FILE NAME:		
UNLESS OTHERWISE SPECIFIED DIMENSIONAL TOLERANCE ARE: mm [IN]		MATERIAL/COLOR: N/A
Tolerance(mm) 0<L<50 ±0.5 50<L<250 ±1.0 250<L<500 ±1.5 500<L<1000 ±2.5 1000<L<2000 ±4.0		DRAWING NUMBER: P24D01G-XXYZ_DC
THIRD ANGLE PROJECTION	DRAWN BY: LWB DATE: 10/11/2023	CHK: SEAN SCALE: NONE SHT 2 OF 2
		SCALE: B

2



1