

TX6A™ Category 6A U/UTP Outside Plant (OSP) Copper Cable

specifications

Category 6A OSP cable shall meet the IEC 61156-5 and ANSI/TIA-568.2-D Category 6A component Standards. The conductors shall be 23 AWG with foamed polyethylene insulation. The cable shall have a gel-filled construction to prevent moisture migration in underground and wet applications and a wide temperature range for extreme weather environments. The copper conductors shall be twisted in pairs, separated by a pair separator, covered with an alien crosstalk barrier and a UV-resistant and abrasion-resistant polyethylene (PE) jacket. Alien crosstalk barrier should not be grounded. **Product is to be used in duct and conduit installations only. Not to be used in aerial or direct burial installations.**



TX6A U/UTP (OSP) Copper Cable

OSP: **PUO6X04BL-CEG**

Country of Origin, China: PUO6X04BL-CEG and PUO6X04WH-CEG

technical information

Electrical performance:	Certified channel performance in a 4-connector configuration up to 100m and exceeds ISO 11801 Class E _A and ANSI/TIA-568.2-D Category 6A Standards for supporting 10GBASE-T transmission over twisted-pair cabling systems as part of the TX6A Copper Cabling System. Certified component performance up to 100m and exceeds the IEC 61156-5 and ANSI/TIA-568.2-D Category 6A Standards for supporting 10GBASE-T transmission over twisted-pair cabling.
Conductor/insulator:	23 AWG solid copper insulated with foamed polyethylene
Installation diameter:	0.044" – 0.053" (1.13 – 1.34mm)
Standards compliance:	ISO 11801 Class E _A , IEC 61156-5 Category 6A, ANSI/TIA-568.2-D Category 6A, IEC 60794-1-2F5 Method B Water Penetration Requirement
Flame rating:	EN50575: Euroclass Fca6
PoE compliance:	Meets IEEE 802.3af, IEEE 802.3at, and IEEE 802.3bt for PoE applications
Installation tension:	110 N (25 lbf) maximum
Temperature rating:	-40°F to 176°F (-40°C to 80°C) during operation 32°F to 122°F (0°C to 50°C) during installation
Cable jacket:	Black UV- and abrasion-resistant polyethylene (PE)
Cable diameter:	0.323" (8.2mm) nominal
Cable weight:	71 lbs./1000' (32 kg/305m)
Packaging:	1000' (305m) reel Packaged tested to ISTA procedure 1A

key features and benefits

Bulk packaging:	Ensures proper performance and provides quick installation
Descending length cable markings:	Print legend contains markings from 1000' to 0'
Robust design:	Overall barrier provides superior alien crosstalk and electrical performance
Flooding compound:	Waterproof gel prevents moisture migration and water ingress

applications

TX6A OSP Unshielded Copper Cable is a component of the TX6A Copper Cabling System. This end-to-end system provides a cost-effective media for ensuring the most challenging network bandwidth needs are easily met today and tomorrow. Businesses are placing increased reliance on their networks to efficiently pass vital and time sensitive information throughout their enterprise.

Key applications include:

- 10GBASE-T Ethernet
- 1000BASE-T Gigabit Ethernet
- 10/100BASE-T Ethernet
- Broadband Video
- POE, POE+, POE++


PRODUCT IS TO BE USED IN DUCT AND CONDUIT INSTALLATIONS ONLY. NOT TO BE USED IN AERIAL OR DIRECT BURIAL APPLICATIONS.

TX6A™ Category 6A U/UTP OutsidePlant (OSP) Copper Cable

additional specifications

Mechanical Test	
Ultimate Breaking Strength	>400 N (90 lbf)
Minumum Bend Radius	8x cable diameterr
Electrical Test	
Nominal Velocity of Propagation (NVP)	65% nominal
Operating Voltage, Maximum	80 V

cable construction



WORLDWIDE SUBSIDIARIES AND SALES OFFICES

PANDUIT US/CANADA
Phone: 800.777.3300

PANDUIT EUROPE LTD.
London, UK
Phone: 44.20.8601.7200

PANDUIT SINGAPORE PTE. LTD.
Republic of Singapore
Phone: 65.6305.7575

PANDUIT JAPAN
Tokyo, Japan
Phone: 81.3.6863.6000

PANDUIT LATIN AMERICA
Guadalajara, Mexico
Phone: 52.33.3777.6000

PANDUIT AUSTRALIA PTY. LTD.
Victoria, Australia
Phone: 61.3.9794.9020

For a copy of Panduit product warranties, log on to www.panduit.com/warranty

PANDUIT®

For more information
Visit us at www.panduit.com
Contact Customer Service by email: cs@panduit.com
or by phone: 800.777.3300

© 2023 Panduit Corp.
ALL RIGHTS RESERVED.
COSP515-WW-ENG
6/2023