

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	WEIGHT
SEE SHEET 2	SEE SHEET 2

SPECIFICATION:

1. STANDARD:

UNIT TYPE:	SEE SHEET 2
ORIENTATION:	VERTICAL, 0U, FULL
OUTLET QTY&TYPE:	(24) C13, (8) C19
INPUT VOLTAGE:	200-240VAC
INPUT CURRENT:	32A / 30A (24A DERATED)
BREAKER QTY&TYPE:	(2) 20AMP, SINGLE-POLE
INPUT PHASE:	SINGLE-PHASE
RATED POWER:	7.4 / 5.8kVA (DUAL RATED)
INPUT PLUG:	IEC 60309 2P+E 6H 32A/30A(24A DERATED)
INPUT POWER CORD:	SEE SHEET 2 FOR PART NUMBER TABLE
REGULATORY STANDARD:	RoHS COMPLIANT

2. ADDITIONAL:
PDU TO BE WIRED LINE TO NEUTRAL






3. ACCESSORIES:
(1) QUICK-START GUIDE

NOTES:

- PRIMARY DIMENSIONS ARE IN MILLIMETERS. SECONDARY DIMENSION ARE IN [INCHES]
- INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE, AND LOCAL CODES
- VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART
- FOR FULL PRODUCT FUNCTIONALITY REFER TO USER MANUAL
- DRAWING VIEWS SHOW THE INPUT CORD IN THE "TOP END FED" CONFIGURATION

IDENTIFICATION
FOR FINISHED GOOD PART NUMBER & DESCRIPTION TABLE SEE SHEET 2 CONFIGURABLE PART NUMBERS: P32E06M-XX Y Z

XX: FINISHED GOOD COLOR BL=BLACK YL=YELLOW RD=RED BU=BLUE WH=WHITE GN=GREEN	Y: INPUT FEED TYPE 1=TOP-END FED 2=BOTTOM-END FED	Z: INPUT CORD LENGTH A=1 METER B=2 METER C=3 METER
--	---	---



PLUG/RECEPTACLE BLOCK

PLUG
IEC 60309, 2P 3W, 6H
IP44 (SPLASHPROOF)
32A /30A(24A DERATED)
230-400V MAX RATED INPUT

RECEPTACLES
IEC 60320/C19
16A, 250V MAX RATED OUTPUT

RECEPTACLES
IEC 60320/C13
10A, 250V MAX RATED OUTPUT

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
06A	12/16/2022	ZLF	MIM	MJD	1.UPDATED P32E06M TO DUAL RATED 2.CHANGE THE CURRENT OF BREAKER FROM 16A TO 20A 3.DELETE UPGRADEABLE PDU OPTION	P32E06M
05A	05/10/2022	FYZ	MIM	MJD	1.ADDED UPGRADEABLE PDU OPTION 2.REMOVED OBSOLETE SKU'S	P32E06M
04A	06/11/2020	CWW	MIM	JAWI	UPDATED THE OUTLET DESIGN	P32E06M
03A	06/07/2018	H.XU	MIM	JAWI	ADDED "BOTTOM-END FED" CONFIGURABLE PART NUMBER TO SHEET 2 TABLE AND DESCRIPTION. UPDATED IDENTIFICATION TO INCLUDE "BOTTOM-END FED" IN CONFIGURABLE OPTION DE-CODER UPDATED CIRCUIT BREAKER LABELS WITH ROTATED TEXT	P32E06M
02A	02/24/2018	H.XU	MIM	JAWI	ADDED SHEET 2 WITH CONFIGURABLE PART NUMBER TABLE AND DESCRIPTION UPDATED IDENTIFICATION TO INCLUDE CONFIGURABLE OPTION "DE-CODER"	P32E06M
01B	12/14/2017	GEORGE	MIM	EDM	UPDATED DESCRIPTION	P32E06M
01A	07/31/2017	GEORGE	MIM	EDM	INITIAL RELEASE	P32E06M

WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGN THE CLIENT SIGNATURE BOX. THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY

SIGN _____
DATE _____
PRINT _____

TITLE: INTELLIGENT SERIES PDU
P32E06M-XXYZ
CUSTOMER DRAWING

ITEM REVISION NAME: _____
DATASHEET FILE NAME: _____

UNLESS OTHERWISE SPECIFIED
DIMENSIONAL TOLERANCE ARE: mm [IN]

Tolerance(mm)	
0<L<50	±0.5
50<L<250	±1.0
250<L<500	±1.5
500<L<1000	±2.5
1000<L<2000	±4.0

MATERIAL/COLOR: N/A

DRAWING NUMBER: P32E06M_DC

THIRD ANGLE PROJECTION

DRAWN BY: GEORGE DATE: 07/31/2017 CHK: SEAN SCALE: NONE

SHT 1 OF 2 SCALE: B

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

MAIN PDU CONFIGURATIONS				
FINISHED GOOD PART NUMBER	FINISHED GOOD DESCRIPTION	COLOR	INPUT CORD LENGTH	WEIGHT
P32E06M	VERTICAL,(24) C13,(8) C19,MONITORED SWITCHED, 200-240V/32/30AMP/1 PHASE , TOP-END FED, 3 METER INPUT CORD, BLACK	BLACK (RAL 9005)	3M(+254MM-127MM) 10'[+10"/-5"]	6.5kg
P32E06M-BL1A	VERTICAL,(24) C13,(8) C19,MONITORED SWITCHED, 200-240V/32/30AMP/1 PHASE , TOP-END FED, 1 METER INPUT CORD, BLACK	BLACK (RAL 9005)	1M(+178MM-89MM) 3.3'[+3.5"/-1.75"]	5.9kg
P32E06M-RD1A	VERTICAL,(24) C13,(8) C19,MONITORED SWITCHED, 200-240V/32/30AMP/1 PHASE , TOP-END FED, 1 METER INPUT CORD, RED	RED (RAL 3020)	1M(+178MM-89MM) 3.3'[+3.5"/-1.75"]	5.9kg
P32E06M-RD1C	VERTICAL,(24) C13,(8) C19,MONITORED SWITCHED, 200-240V/32/30AMP/1 PHASE , TOP-END FED, 3 METER INPUT CORD, RED	RED (RAL 3020)	3M(+254MM-127MM) 10'[+10"/-5"]	6.5kg
P32E06M-YL1A	VERTICAL,(24) C13,(8) C19,MONITORED SWITCHED, 200-240V/32/30AMP/1 PHASE , TOP-END FED, 1 METER INPUT CORD, YELLOW	YELLOW (RAL 1023)	1M(+178MM-89MM) 3.3'[+3.5"/-1.75"]	5.9kg
P32E06M-YL1C	VERTICAL,(24) C13,(8) C19,MONITORED SWITCHED, 200-240V/32/30AMP/1 PHASE , TOP-END FED, 3 METER INPUT CORD, YELLOW	YELLOW (RAL 1023)	3M(+254MM-127MM) 10'[+10"/-5"]	6.5kg
P32E06M-BU1A	VERTICAL,(24) C13,(8) C19,MONITORED SWITCHED, 200-240V/32/30AMP/1 PHASE , TOP-END FED, 1 METER INPUT CORD, BLUE	BLUE (RAL 5005)	1M(+178MM-89MM) 3.3'[+3.5"/-1.75"]	5.9kg
P32E06M-BU1C	VERTICAL,(24) C13,(8) C19,MONITORED SWITCHED, 200-240V/32/30AMP/1 PHASE , TOP-END FED, 3 METER INPUT CORD, BLUE	BLUE (RAL 5005)	3M(+254MM-127MM) 10'[+10"/-5"]	6.5kg
P32E06M-BL2A	VERTICAL,(24) C13,(8) C19,MONITORED SWITCHED, 200-240V/32/30AMP/1 PHASE , BOTTOM-END FED, 1 METER INPUT CORD, BLACK	BLACK (RAL 9005)	1M(+178MM-89MM) 3.3'[+3.5"/-1.75"]	5.9kg
P32E06M-BL2C	VERTICAL,(24) C13,(8) C19,MONITORED SWITCHED, 200-240V/32/30AMP/1 PHASE , BOTTOM-END FED, 3 METER INPUT CORD, BLACK	BLACK (RAL 9005)	3M(+254MM-127MM) 10'[+10"/-5"]	6.5kg
P32E06M-RD2A	VERTICAL,(24) C13,(8) C19,MONITORED SWITCHED, 200-240V/32/30AMP/1 PHASE , BOTTOM-END FED, 1 METER INPUT CORD, RED	RED (RAL 3020)	1M(+178MM-89MM) 3.3'[+3.5"/-1.75"]	5.9kg
P32E06M-RD2C	VERTICAL,(24) C13,(8) C19,MONITORED SWITCHED, 200-240V/32/30AMP/1 PHASE , BOTTOM-END FED, 3 METER INPUT CORD, RED	RED (RAL 3020)	3M(+254MM-127MM) 10'[+10"/-5"]	6.5kg
P32E06M-YL2A	VERTICAL,(24) C13,(8) C19,MONITORED SWITCHED, 200-240V/32/30AMP/1 PHASE , BOTTOM-END FED, 1 METER INPUT CORD, YELLOW	YELLOW (RAL 1023)	1M(+178MM-89MM) 3.3'[+3.5"/-1.75"]	5.9kg
P32E06M-YL2C	VERTICAL,(24) C13,(8) C19,MONITORED SWITCHED, 200-240V/32/30AMP/1 PHASE , BOTTOM-END FED, 3 METER INPUT CORD, YELLOW	YELLOW (RAL 1023)	3M(+254MM-127MM) 10'[+10"/-5"]	6.5kg
P32E06M-BU2A	VERTICAL,(24) C13,(8) C19,MONITORED SWITCHED, 200-240V/32/30AMP/1 PHASE , BOTTOM-END FED, 1 METER INPUT CORD, BLUE	BLUE (RAL 5005)	1M(+178MM-89MM) 3.3'[+3.5"/-1.75"]	5.9kg
P32E06M-BU2C	VERTICAL,(24) C13,(8) C19,MONITORED SWITCHED, 200-240V/32/30AMP/1 PHASE , BOTTOM-END FED, 3 METER INPUT CORD, BLUE	BLUE (RAL 5005)	3M(+254MM-127MM) 10'[+10"/-5"]	6.5kg

06A	12/16/2022	ZLF	MIM	MJD	1.UPDATED P32E06M TO DUAL RATED 2.CHANGE THE CURRENT OF BREAKER FROM 16A TO 20A 3.DELETE UPGRADEABLE PDU OPTION	P32E06M
05A	05/10/2022	FYZ	MIM	MJD	1.ADDED UPGRADEABLE PDU OPTION 2.REMOVED OBSOLETE SKU'S	P32E06M
04A	06/11/2020	CWW	MIM	JAWI	UPDATED THE OUTLET DESIGN	P32E06M
03A	06/07/2018	H.XU	MIM	JAWI	ADDED 'BOTTOM-END FED' CONFIGURABLE PART NUMBER TO SHEET 2 TABLE AND DESCRIPTION. UPDATED IDENTIFICATION TO INCLUDE 'BOTTOM-END FED' IN CONFIGURABLE OPTION DE-CODER UPDATED CIRCUIT BREAKER LABELS WITH ROTATED TEXT	P32E06M
02A	02/24/2018	H.XU	MIM	JAWI	ADDED SHEET 2 WITH CONFIGURABLE PART NUMBER TABLE AND DESCRIPTION UPDATED IDENTIFICATION TO INCLUDE CONFIGURABLE OPTION 'DE-CODER'	P32E06M
01B	12/14/2017	GEORGE	MIM	EDM	UPDATED DESCRIPTION	P32E06M
01A	07/31/2017	GEORGE	MIM	EDM	INITIAL RELEASE	P32E06M
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN

WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGN THE CLIENT SIGNATURE BOX. THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY

SIGN _____
DATE _____
PRINT _____

TITLE: INTELLIGENT SERIES PDU
P32E06M-XXYZ
CUSTOMER DRAWING

ITEM REVISION NAME: _____

DATASHEET FILE NAME: _____

UNLESS OTHERWISE SPECIFIED
DIMENSIONAL TOLERANCE ARE: mm [IN]

Tolerance(mm)	
0<L<50	±0.5
50<L<250	±1.0
250<L<500	±1.5
500<L<1000	±2.5
1000<L<2000	±4.0

MATERIAL/COLOR: N/A

DRAWING NUMBER: P32E06M_DC

THIRD ANGLE PROJECTION

DRAWN BY: GEORGE DATE: 07/31/2017

CHK: SEAN SCALE: NONE

SHT 2 OF 2

SCALE: B