


NetKey® Category 5e Component-Rated Punchdown Jack Modules

SPECIFICATIONS

Category 5e/Class D 8-position, industry standard keystone jack module terminates 4-pair, 22 – 26 AWG, 100 ohm unshielded pair cable. Jack module uses a punchdown tool to properly and securely terminate each conductor for optimum performance. The jack module contains a color coded label for T568A and T568B wiring schemes. A retention cap provides additional strain relief.



TECHNICAL INFORMATION

Category 5e/Class D performance:	Exceeds ANSI/TIA-568-C.2 Category 5e and ISO 11801 Class D channel requirements at swept frequencies up to 100 MHz Meets ANSI/TIA-568-C.2 and ISO 11801 Category 5e component requirements at swept frequencies up to 100 MHz
FCC compliance:	Complies with ANSI/TIA-1096-A (formerly FCC Part 68); contacts plated with 50 microinches of gold for superior performance
IEC compliance:	Meets IEC 60603-7
PoE compliance:	Supports IEEE 802.3af/802.3at and proposed 802.3bt type 3 and type 4 PoE applications
Safety compliance:	cULus Listed; UL 1863 and CAN/CSA-C22.2 (UL File E129886)
RoHS compliance:	Compliant

KEY FEATURES AND BENEFITS

100% Performance tested:	Confidence that each jack module delivers specified performance
110 style punchdown termination:	Utilizes industry standard termination style and includes wire retention cap
Modular:	Universal keystone jack modules snap in and out of all NetKey® Faceplates, Modular Patch Panels, and Surface Mount Boxes for fast moves, adds, and changes
Individually serialized:	Marked with quality control number for future traceability
Convenience packaging (optional):	25 jacks packaged in one easy to open container, eliminating the time to open each individual package and reducing on-site waste; ideal for high volume installations

APPLICATIONS

Applications include:

- Ethernet 10BASE-T, 100BASE-T (Fast Ethernet), and 1000BASE-T (Gigabit Ethernet)
- 155 Mb/s ATM, 622 Mb/s ATM, 1.2 Gb/s ATM
- Token Ring 4/16
- Voice over internet protocol (VoIP)

NetKey Jack Modules

Module:	NKP5E88M*
25 Pack:	NKP5E88M*- Q

NetKey Patch Cords

Foot lengths:	NK5EPC^**Y
Meter lengths:	NK5EPC^^M***Y

Termination and Cable Prep Tools

Punchdown tool:	PDT110‡
Punchdown base:	NKSPB
JackRapid® Termination Tool:	JR-PAN-2‡‡
Cable snipping tool:	CWST
Cable stripping tool:	CJAST

^Feet lengths: 3, 5, 7, 10, 14 or 20 meters

^^Meter lengths: 1, 2, 3, 4, or 5 meters

*Colors: IW (Off White), EI (Electric Ivory), IG (Int'l Gray), WH (White), BL (Black), OR (Orange), RD (Red), BU (Blue), GR (Green) or YL (Yellow)

**Colors other than Off White: (Blue), GR (Green), RD (Red) or YL (Yellow)

***Colors other than Off White: BU (Blue), GR (Green), RD (Red) or YL (Yellow)

-24 indicates bulk packages of 24 pieces per package to reduce single-use plastic

-Q indicates bulk packages of 25 pieces per package to reduce single-use plastic

‡Terminates the NetKey Keystone Punchdown Jack Module and NetKey Patch Panel.

‡‡Terminates the NetKey Keystone Punchdown Jack Module.

Fluke JackRapid Termination Tool available through distribution. To locate the local office, visit www.flukenetworks.com/contact




+JackRapid is a trademark of Fluke Networks.

NetKey® Category 5e Component-Rated Punchdown Jack Modules

NETKEY CATEGORY 5E ELECTRICAL PERFORMANCE

Parameters	dB @ 100 MHz
NEXT	> 43.0
FEXT	> 35.1
Attenuation	< 0.40
Return Loss	> 20.0

ENGINEERING DRAWINGS



Dimensions are in inches. [Dimensions in brackets are metric].

WORLDWIDE SUBSIDIARIES AND SALES OFFICES

PANDUIT US/CANADA
Phone: 800.777.3300

PANDUIT EUROPE LTD.
London, UK
Phone: 44.20.8601.7200

PANDUIT SINGAPORE PTE. LTD.
Republic of Singapore
Phone: 65.6305.7575

PANDUIT JAPAN
Tokyo, Japan
Phone: 81.3.6863.6000

PANDUIT LATIN AMERICA
Guadalajara, Mexico
Phone: 52.33.3777.6000

PANDUIT AUSTRALIA PTY. LTD.
Victoria, Australia
Phone: 61.3.9794.9020

For a copy of Panduit product warranties, log on to www.panduit.com/warranty



For more information
Visit us at www.panduit.com
Contact Customer Service by email: cs@panduit.com
or by phone: 800.777.3300

© 2024 Panduit Corp.
ALL RIGHTS RESERVED.
COSP599-WW-ENG
7/2024