






THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	WEIGHT
SEE SHEET 2	SEE SHEET 2



**SPECIFICATION:**

1. STANDARD:	
UNIT TYPE:	MONITORED INPUT
ORIENTATION:	VERTICAL, 0U FULL
OUTLET QTY & TYPE:	(36) C13, (6) C19
INPUT VOLTAGE:	200-240/346-415VAC
INPUT CURRENT:	30A(24A DERATED)
BREAKER QTY & TYPE:	(6) 20AMP, SINGLE-POLE, 10KA
INPUT PHASE:	THREE-PHASE, WYE
RATED POWER:	17.3 kVA
INPUT PLUG:	L22-30P
INPUT POWER CORD:	SEE SHEET 2 FOR PART NUMBER TABLE
REGULATORY STANDARD:	RoHS COMPLIANT

2. ADDITIONAL:  
THE G6 CONTROLLER IS NOT BACKWARDS COMPATIBLE WITH ANY LEGACY CONTROLLERS

3. ACCESSORIES:  
DOCUMENTATION KIT  
PRODUCT SAFETY WARNING SHEET

**NOTES:**

- PRIMARY DIMENSIONS ARE IN MILLIMETERS. SECONDARY DIMENSION ARE IN [ INCHES ] .
- INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE, AND LOCAL CODES .
- VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART .
- FOR FULL PRODUCT FUNCTIONALITY REFER TO USER MANUAL .
- DRAWING VIEWS SHOW THE INPUT CORD IN THE "TOP END FED" CONFIGURATION

**IDENTIFICATION**  
FOR FINISHED GOOD PART NUMBER & DESCRIPTION TABLE SEE SHEET 2 CONFIGURABLE PART NUMBERS: **P42D07G-XX Y Z**

<b>XX: FINISHED GOOD COLOR</b> BL =BLACK RD =RED WH =WHITE YL =YELLOW BU =BLUE GN =GREEN	<b>Y: INPUT FEED TYPE</b> 1 =TOP-END FED 2 =BOTTOM-END FED	<b>Z: INPUT CORD LENGTH</b> A =1 METER B =2 METER C =3 METER
--	--	---

B

B

A

A

**PLUG/RECEPTACLE BLOCK**

PLUG  
NEMA L22-30P,4P 5W  
30A, 120/208V MAX RATED INPUT  
24A DERATED

RECEPTACLES  
IEC 60320/C19  
16A, 250V MAX RATED OUTPUT

RECEPTACLES  
IEC 60320/C13  
10A, 250V MAX RATED OUTPUT

00A	09/21/2023	NW	CSH	MJD	INITIAL RELEASE	P42D07G-XXYZ			
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN			

WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGN THE CLIENT SIGNATURE BOX. THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY.	SIGN DATE PRINT
TITLE: INTELLIGENT SERIES PDU P42D07G-XXYZ CONTROL DRAWING	
ITEM REVISION NAME: DATASHEET FILE NAME:	
UNLESS OTHERWISE SPECIFIED DIMENSIONAL TOLERANCE ARE: mm [IN]	MATERIAL/COLOR:  N/A
Tolerance(mm) 0<L<50 ±0.5 50<L<250 ±1.0 250<L<500 ±1.5 500<L<1000 ±2.5 1000<L<2000 ±4.0	DRAWING NUMBER: P42D07G-XXYZ_DC
THIRD ANGLE PROJECTION	SCALE NONE
DRAWN BY: NW DATE: 09/06/2023 CHK: CSH	SHT 1 OF 2 SCALE: B

2

1



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

FINISHED GOOD PART NUMBER	FINISHED GOOD DESCRIPTION	COLOR	INPUT CORD LENGTH	WEIGHT
P42D07G	G6 MI PDU, 30AMP, (36) C13 (6) C19, NEMA L22-30P-3M, TOP FED, BLACK	BLACK (RAL 9005)	3M(+254MM-127MM) 10'(+10"/-5")	9.5kg

B

B

A

A

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
00A	09/21/2023	NW	CSH	MJD	INITIAL RELEASE	P42D07G-XXYZ

WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGN THE CLIENT SIGNATURE BOX. THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY		SIGN
		DATE
		PRINT
TITLE: INTELLIGENT SERIES PDU P42D07G-XXYZ CONTROL DRAWING		
ITEM REVISION NAME:		<b>PANDUIT</b>
DATASHEET FILE NAME:		
UNLESS OTHERWISE SPECIFIED DIMENSIONAL TOLERANCE ARE: mm [IN]		MATERIAL/COLOR: N/A
THIRD ANGLE PROJECTION Tolerance(mm) 0<L450 ±0.5 50<L250 ±1.0 250<L500 ±1.5 500<L1000 ±2.5 1000<L2000 ±4.0		DRAWING NUMBER: P42D07G-XXYZ_DC
DRAWN BY	DATE	SCALE
NW	09/06/2023	NONE
CHK	SCALE	SHT 2 OF 2
CSH	NONE	B

