



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	WEIGHT
SEE SHEET 2	SEE SHEET 2




LEFT VIEW




REAR VIEW

TOOLESS MOUNTING
BUTTON LOCATIONS (12) PL



RIGHT VIEW

FOR LENGTH
SEE SHEET 2
PART NUMBER
TABLE.



FRONT VIEW

SPECIFICATION:


- STANDARD:
 - UNIT TYPE: SEE SHEET 2
 - ORIENTATION: VERTICAL, 0U FULL
 - OUTLET QTY & TYPE: (30) C13, (12) C19
 - INPUT VOLTAGE: 200-240/346-415VAC
 - JAPAN INPUT VOLTAGE: 346-415VAC
 - INPUT CURRENT: 32A
 - BREAKER QTY & TYPE: (6) 16AMP, SINGLE-POLE THREE-PHASE WYE
 - RATED POWER: 22.0 kVA
 - INPUT PHASE: IEC 60309 3P+N+E 6H 32A
 - INPUT PLUG: SEE SHEET 2 FOR PART NUMBER TABLE
 - INPUT POWER CORD: SEE SHEET 2 FOR PART NUMBER TABLE
 - REGULATORY STANDARD: RoHS COMPLIANT
- ADDITIONAL: NONE
- ACCESSORIES: (1) QUICK-START GUIDE

NOTES:

- PRIMARY DIMENSIONS ARE IN MILLIMETERS. SECONDARY DIMENSION ARE IN [INCHES]
- INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE, AND LOCAL CODES
- VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART
- FOR FULL PRODUCT FUNCTIONALITY REFER TO USER MANUAL
- DRAWING VIEWS SHOW THE INPUT CORD IN THE "TOP END FED" CONFIGURATION
- PARTS USING UPGRADEABLE iPDU BLANKING PANEL CAN BE UPGRADED TO INTELLIGENT MODELS USING PANDUIT CONTROLLER PART NUMBER MA002

IDENTIFICATION

FOR FINISHED GOOD PART NUMBER & DESCRIPTION TABLE SEE SHEET 2 CONFIGURABLE PART NUMBERS: **P42D04M-XX Y Z**



BOTTOM VIEW

PLUG/RECEPTACLE BLOCK



PLUG
IEC 60309, 4P 5W, 6H
IP44 (SPLASHPROOF)
32A, 346 415V MAX RATED INPUT



RECEPTACLES
IEC 60320/C19
16A, 250V MAX RATED OUTPUT



RECEPTACLES
IEC 60320/C13
10A, 250V MAX RATED OUTPUT

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
05A	05/18/2022	FYZ	MIM	MJD	1.ADDED UPGRADEABLE PDU OPTION 2.REMOVED OBSOLETE SKU'S	P42D04M
04B	03/03/2022	LWB	MIM	JAWI	UPDATED THE COMPLIANCE LABEL TO INCLUDE THE UCKA LOGO	P42D04M
04A	05/09/2019	MIM	DACU	JAWI	ADDED "JAPAN INPUT VOLTAGE:346-415VAC" TO SPECIFICATION NOTE 1,SHT 1 ADDED "JAPAN INPUT:346-415VAC,WYE,3ø,50/60Hz,32A" TO COMPLIANCE LABEL,SHT3 COMPLIANCE LABEL "MAC Address" "WAS" "Mac Address"	P42D04M
03A	06/07/2018	H.XU	MIM	JAWI	ADDED SHEET 2 WITH CONFIGURABLE PART NUMBER TABLE AND DESCRIPTION UPDATED IDENTIFICATION TO INCLUDE CONFIGURABLE OPTION 'DE-CODER'	P42D04M
-	-	-	-	-	UNRELEASED REVISION	-
01A	07/17/2017	WSJ	MIM	EDM	INITIAL RELEASE	P42D04M

WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGN THE CLIENT SIGNATURE BOX. THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY.		SIGN
		DATE
		PRINT
TITLE		
INTELLIGENT SERIES PDU P42D04M-XXYZ CUSTOMER DRAWING		
ITEM REVISION NAME		PANDUIT
DATASHEET FILE NAME:		
UNLESS OTHERWISE SPECIFIED DIMENSIONAL TOLERANCE ARE: mm [IN]		MATERIAL/COLOR:
Tolerance(mm)		N/A
0<L<50 ±0.5		DRAWING NUMBER: P42D04M_DC
50<L<250 ±1.0		
250<L<500 ±1.5		
500<L<1000 ±2.5		
1000<L<2000 ±4.0		
DRAWN BY	DATE	SCALE
WSJ	07/17/2017	NONE
CHK	SEAN	
SHT 1 OF 2		SCALE B



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

MAIN PDU CONFIGURATIONS				
FINISHED GOOD PART NUMBER	FINISHED GOOD DESCRIPTION	COLOR	INPUT CORD LENGTH	WEIGHT
P42D04M	VERTICAL,(30) C13,(12)C19,MONITORED INPUT, 200-240/346-415V/32A/3 PHASE WYE, TOP-END FED, 3 METER INPUT CORD, BLACK	BLACK (RAL 9005)	3M(+254MM/-127MM) 10'[+10"/-5"]	10.9kg
P42D04M-BL1A	VERTICAL,(30) C13,(12)C19,MONITORED INPUT, 200-240/346-415V/32A/3 PHASE WYE, TOP-END FED, 1 METER INPUT CORD, BLACK	BLACK (RAL 9005)	1M(+178MM/-89MM) 3.3'[+3.5"/-1.75"]	9.7kg
P42D04M-RD1A	VERTICAL,(30) C13,(12)C19,MONITORED INPUT, 200-240/346-415V/32A/3 PHASE WYE, TOP-END FED, 1 METER INPUT CORD, RED	RED (RAL 3020)	1M(+178MM/-89MM) 3.3'[+3.5"/-1.75"]	9.7kg
P42D04M-RD1C	VERTICAL,(30) C13,(12)C19,MONITORED INPUT, 200-240/346-415V/32A/3 PHASE WYE, TOP-END FED, 3 METER INPUT CORD, RED	RED (RAL 3020)	3M(+254MM/-127MM) 10'[+10"/-5"]	10.9kg
P42D04M-YL1A	VERTICAL,(30) C13,(12)C19,MONITORED INPUT, 200-240/346-415V/32A/3 PHASE WYE, TOP-END FED, 1 METER INPUT CORD, YELLOW	YELLOW (RAL 1023)	1M(+178MM/-89MM) 3.3'[+3.5"/-1.75"]	9.7kg
P42D04M-YL1C	VERTICAL,(30) C13,(12)C19,MONITORED INPUT, 200-240/346-415V/32A/3 PHASE WYE, TOP-END FED, 3 METER INPUT CORD, YELLOW	YELLOW (RAL 1023)	3M(+254MM/-127MM) 10'[+10"/-5"]	10.3kg
P42D04M-BU1A	VERTICAL,(30) C13,(12)C19,MONITORED INPUT, 200-240/346-415V/32A/3 PHASE WYE, TOP-END FED, 1 METER INPUT CORD, BLUE	BLUE (RAL 5005)	1M(+178MM/-89MM) 3.3'[+3.5"/-1.75"]	9.7kg
P42D04M-BU1C	VERTICAL,(30) C13,(12)C19,MONITORED INPUT, 200-240/346-415V/32A/3 PHASE WYE, TOP-END FED, 3 METER INPUT CORD, BLUE	BLUE (RAL 5005)	3M(+254MM/-127MM) 10'[+10"/-5"]	10.9kg
P42D04M-BL2A	VERTICAL,(30) C13,(12)C19,MONITORED INPUT, 200-240/346-415V/32A/3 PHASE WYE, BOTTOM-END FED, 1 METER INPUT CORD, BLACK	BLACK (RAL 9005)	1M(+178MM/-89MM) 3.3'[+3.5"/-1.75"]	9.7kg
P42D04M-BL2C	VERTICAL,(30) C13,(12)C19,MONITORED INPUT, 200-240/346-415V/32A/3 PHASE WYE, BOTTOM-END FED, 3 METER INPUT CORD, BLACK	BLACK (RAL 9005)	3M(+254MM/-127MM) 10'[+10"/-5"]	10.9kg
P42D04M-RD2A	VERTICAL,(30) C13,(12)C19,MONITORED INPUT, 200-240/346-415V/32A/3 PHASE WYE, BOTTOM-END FED, 1 METER INPUT CORD, RED	RED (RAL 3020)	1M(+178MM/-89MM) 3.3'[+3.5"/-1.75"]	9.7kg
P42D04M-RD2C	VERTICAL,(30) C13,(12)C19,MONITORED INPUT, 200-240/346-415V/32A/3 PHASE WYE, BOTTOM-END FED, 3 METER INPUT CORD, RED	RED (RAL 3020)	3M(+254MM/-127MM) 10'[+10"/-5"]	10.9kg
P42D04M-YL2A	VERTICAL,(30) C13,(12)C19,MONITORED INPUT, 200-240/346-415V/32A/3 PHASE WYE, BOTTOM-END FED, 1 METER INPUT CORD, YELLOW	YELLOW (RAL 1023)	1M(+178MM/-89MM) 3.3'[+3.5"/-1.75"]	9.7kg
P42D04M-YL2C	VERTICAL,(30) C13,(12)C19,MONITORED INPUT, 200-240/346-415V/32A/3 PHASE WYE, BOTTOM-END FED, 3 METER INPUT CORD, YELLOW	YELLOW (RAL 1023)	3M(+254MM/-127MM) 10'[+10"/-5"]	10.3kg
P42D04M-BU2A	VERTICAL,(30) C13,(12)C19,MONITORED INPUT, 200-240/346-415V/32A/3 PHASE WYE, BOTTOM-END FED, 1 METER INPUT CORD, BLUE	BLUE (RAL 5005)	1M(+178MM/-89MM) 3.3'[+3.5"/-1.75"]	9.7kg
P42D04M-BU2C	VERTICAL,(30) C13,(12)C19,MONITORED INPUT, 200-240/346-415V/32A/3 PHASE WYE, BOTTOM-END FED, 3 METER INPUT CORD, BLUE	BLUE (RAL 5005)	3M(+254MM/-127MM) 10'[+10"/-5"]	10.9kg
UPGRADEABLE PDU CONFIGURATIONS				
FINISHED GOOD PART NUMBER	FINISHED GOOD DESCRIPTION	COLOR	INPUT CORD LENGTH	WEIGHT
P42D04U	UPGRADEABLE,VERTICAL,(30) C13,(12)C19,MONITORED INPUT, 200-240/346-415V/32A/3 PHASE WYE, TOP-END FED, 3 METER INPUT CORD, BLACK	BLACK (RAL 9005)	3M(+254MM/-127MM) 10'[+10"/-5"]	10.6kg

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
05A	05/18/2022	FYZ	MIM	MJD	1.ADDED UPGRADEABLE PDU OPTION 2.REMOVED OBSOLETE SKU'S	P42D04M
04B	03/03/2022	LWB	MIM	JAWI	UPDATED THE COMPLIANCE LABEL TO INCLUDE THE UCKA LOGO	P42D04M
04A	05/09/2019	MIM	DACU	JAWI	ADDED "JAPAN INPUT VOLTAGE:346-415VAC"TO SPECIFICATION NOTE 1,SHT 1 ADDED"JAPAN INPUT:346-415VAC,WYE,3ø,50/60Hz,32A"TO COMPLIANCE LABEL,SHT3 COMPLIANCE LABEL"MAC Address"WAS"Mac Address"	P42D04M
03A	06/07/2018	H.XU	MIM	JAWI	ADDED SHEET 2 WITH CONFIGURABLE PART NUMBER TABLE AND DESCRIPTION UPDATED IDENTIFICATION TO INCLUDE CONFIGURABLE OPTION 'DE-CODER'	P42D04M
	-	-	-	-	UNRELEASED REVISION	-
01A	07/17/2017	WSJ	MIM	EDM	INITIAL RELEASE	P42D04M

WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGN THE CLIENT SIGNATURE BOX. THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY.		SIGN
		DATE
		PRINT
TITLE INTELLIGENT SERIES PDU P42D04M-XXYZ CUSTOMER DRAWING		
ITEM REVISION NAME		
DATASHEET FILE NAME:		
UNLESS OTHERWISE SPECIFIED DIMENSIONAL TOLERANCE ARE: mm [IN]		MATERIAL/COLOR:
Tolerance(mm) 0<L<50 ±0.5 50<L<250 ±1.0 250<L<500 ±1.5 500<L<1000 ±2.5 1000<L<2000 ±4.0		N/A
THIRD ANGLE PROJECTION		DRAWING NUMBER:
		P42D04M_DC
DRAWN BY	DATE	SCALE
WSJ	07/17/2017	NONE
CHK	SCALE	
SEAN	NONE	
SHT 2 OF 2		SCALE
		B

