# NetKey<sup>™</sup> Category 6A UTP Patch Cords

**Asia Pacific** 



#### **SPECIFICATIONS**

Category 6A/Class  $E_A$ , UTP patch cords shall be constructed of 26 AWG twisted pair stranded copper cable with a UTP modular plug on each end. Patch cord cable shall be offered in multiple colors for design flexibility with a strain relief boot on each end. All patch cords shall be wired to be compatible with both T568A and T568B wiring schemes.



### **TECHNICAL INFORMATION**

Category 6A/Class E <sub>A</sub> performance:	Exceeds ANSI/TIA-568.2-D Category 6A and ISO 11801 Class E <sub>A</sub> channel requirements at swept frequencies up to 500 MHz Meets ANSI/TIA-568.2-D and ISO 11801 Category 6 component requirements at swept frequencies up to 250 MHz	
FCC compliance:	Complies with ANSI/TIA-1096A (formerly FCC Part 68); contacts plated with 50 microinches of gold	
IEC compliance:	Meets IEC 60603-7	
PoE compliance:	Supports IEEE 802.3af/802.3at and 802.3bt type 3 and type 4 PoE applications	
c(UL)us compliance:	UL 1863 and CAN/CSA-C22.2 (UL File E129886)	
RoHS compliance:	Compliant	
Cable diameter:	5.9mm (0.023 in.)	
Flame rating:	CM rated	

#### **KEY FEATURES AND BENEFITS**

Performance tested:	Confidence that each patch cord delivers specified performance	
Slender strain relief boot:	Provides easy access in high-density applications	
Common colors and lengths available:	Meets individual length and color-coding requirements	

#### **APPLICATIONS**

Applications include:

- Ethernet 10BASE-T, 100BASE-T (Fast Ethernet), 1000BASE-T (Gigabit Ethernet), 10GBASE-T
- 155 Mb/s ATM, 622 Mb/s ATM, 1.2 Gb/s ATM
- Token Ring 4/16
- Voice over Internet Protocol (VoIP)

NetKey Category 6A UTP Patch Cords

Meter lengths: NKU6APC\*M^

NetKey Category 6A UTP Jack Modules

PD style module: NK6X88M^^

NetKey Patch Panels with Labels

24-port, 1 RU, with 6 NK4MFL:

NKFPL24

48-port, 2 RU, with 12 NK4MFL:

NKFPL48

NetKey Patch Panels with Labels

24-port, 1 RU, with 6 NK4MF:

NKFP24Y

48-port, 2 RU, with 12 NK4MF:

NKFP48Y

Strain Relief Bars

iralli nellel bars

SRBS19BL-XY

Extended 2":
With hook and

Straight:

SRB19BLY SRBM19BLY

loop ties: With adjustable

SRBWCY

clips:

SRB19MDBL


Multi-depth:

\*Meter lengths: 1- 5, 7, or 10 meters ^Color: Blank (Off-White), BU (Blue), RD (Red)

A^Colors: Blank (Off-White), WH (White), AW (Artic White), EI (Electric Ivory), IG (International Gray), BU (Blue), BL (Black), GR (Green), RD (Red), YL (Yellow)

# **NetKey<sup>™</sup> Category 6A UTP Patch Cords**

#### **ENGINEERING DRAWING**



T568B Wiring Scheme		
Plug Position	Cable Wire	
1	White/Orange	
2	Orange	
3	White/Green	
4	Blue	
5	White/Blue	
6	Green	
7	White/Brown	
8	Brown	

Dimensions are in inches. [Dimensions in brackets are metric].

## **WORLDWIDE SUBSIDIARIES AND SALES OFFICES**

PANDUIT US/CANADA Phone: 800.777.3300 PANDUIT EUROPE LTD. London, UK Phone: 44.20.8601.7200 PANDUIT SINGAPORE PTE. LTD. PANDUIT JAPAN Republic of Singapore Phone: 65.6305.7575

Tokyo, Japan Phone: 81.3.6863.6000 PANDUIT LATIN AMERICA Guadalajara, Mexico Phone: 52.33.3777.6000

PANDUIT AUSTRALIA PTY. LTD. Victoria, Australia Phone: 61.3.9794.9020

For a copy of Panduit product warranties, log on to www.panduit.com/warranty



For more information Visit us at www.panduit.com Contact Customer Service by email: cs@panduit.com or by phone: 800.777.3300