


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

NOTES:

- *1. REFER TO www.panduit.com FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE AND PART COLOR
- 2. SPLICING MAY OCCUR FOR ROLL SIZES LONGER THAN 10 FT.
- 3. REVERSE CUT.
- 4. SOME GAP WILL BE PRESENT BETWEEN WINDS
- 5. ALL MATERIALS AND COMPONENTS USED MEET THE MATERIAL RESTRICTIONS OF RoHS (EUROPEAN DIRECTIVE 2011/65/EU ON THE RESTRICTION OF HAZARDOUS SUBSTANCES) AS PROPOSED BY THE RoHS TECHNICAL ADAPTATION COMMITTEE.
- 6. DIMENSIONS IN [] ARE METRIC.

*PANDUIT PART NUMBER	A IN [mm]	B IN [mm]	T IN [mm]	WEIGHT LBS (g)/ 100 FT
T12R	.125 [3.2]	.218 ±.047 [5.5 ±1.2]	.030 ±.006 [0.8 ±0.2]	0.4 (200)
T19R	.188 [4.8]	.250 ±.047 [6.4 ±1.2]	.035 ±.008 [0.9 ±0.2]	0.7 (300)
T25R	.250 [6.4]	.375 ±.047 [9.5 ±1.2]	.040 ±.008 [1.0 ±0.2]	1.2 (550)
T38R	.375 [9.5]	.437 ±.047 [11.1 ±1.2]	.055 ±.010 [1.4 ±0.3]	2.5 (1150)
T50R	.500 [12.7]	.500 ±.047 [12.7 ±1.2]	.060 ±.016 [1.5 ±0.4]	3.7 (1700)
T62R	.625 [15.9]	.625 ±.047 [15.9 ±1.2]	.062 ±.020 [1.6 ±0.5]	4.9 (2250)
T75R	.750 [19.1]	.875 ±.047 [22.2 ±1.2]	.065 ±.020 [1.7 ±0.5]	6.2 (2800)
T100R	1.000 [25.4]	1.125 ±.047 [28.6 ±1.2]	.070 ±.020 [1.8 ±0.5]	9.1 (4150)



PART NUMBER					SEE TABLE														
TITLE										FLAME RESISTANT POLYETHYLENE SPIRAL WRAP									
CUSTOMER DRAWING																			
ITEM REVISION NAME					03903NBC/00														
DATASET FILE NAME					03903NBC_DC/00A														
MATERIAL					POLYETHYLENE					DRAWING NUMBER					03903NBC - DC				
DRAWN BY					KLN					DATE					06/19/2024				
CHK					MSAD					SCALE					NONE				
REV					00A					SHEET 1 OF 1					A				

A-SIZE CUSTOMER