



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.


PANDUIT P/N	WEIGHT
SEE SHEET 2	SEE SHEET 2




LEFT VIEW



REAR VIEW



RIGHT VIEW



FRONT VIEW



BOTTOM VIEW

**SPECIFICATION:**

**1. STANDARD:**

UNIT TYPE:	SEE SHEET 2
ORIENTATION:	VERTICAL, 0U FULL
OUTLET QTY&TYPE:	(28) C13, (6) C19
INPUT VOLTAGE:	200-240VAC
INPUT CURRENT:	32A
BREAKER QTY&TYPE:	(2) 16AMP, SINGLE-POLE
INPUT PHASE:	SINGLE-PHASE
RATED POWER:	7.4kVA
INPUT PLUG:	IEC 60309 2P+E 6H 32A
INPUT POWER CORD:	SEE SHEET 2 FOR PART NUMBER TABLE
REGULATORY STANDARD:	RoHS COMPLIANT

**2. ADDITIONAL:**

NONE

**3. ACCESSORIES:**


(1) QUICK-START GUIDE

**NOTES:**

- PRIMARY DIMENSIONS ARE IN MILLIMETERS. SECONDARY DIMENSION ARE IN [ INCHES ]
- INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE, AND LOCAL CODES
- VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART
- FOR FULL PRODUCT FUNCTIONALITY REFER TO USER MANUAL
- DRAWING VIEWS SHOW THE INPUT CORD IN THE "TOP END FED" CONFIGURATION
- PARTS USING UPGRADEABLE iPDU BLANKING PANEL CAN BE UPGRADED TO INTELLIGENT MODELS USING PANDUIT CONTROLLER PART NUMBER MA002

**IDENTIFICATION**

FOR FINISHED GOOD PART NUMBER & DESCRIPTION TABLE SEE SHEET 2 CONFIGURABLE PART NUMBERS: P34D41M-XX Y Z



**PLUG/RECEPTACLE BLOCK**



PLUG  
IEC 60309, 2P 3W, 6H  
IP44 (SPLASHPROOF)  
32A, 200-250V MAX RATED INPUT



RECEPTACLES  
IEC 60320/C19  
16A, 250V MAX RATED OUTPUT



RECEPTACLES  
IEC 60320/C13  
10A, 250V MAX RATED OUTPUT

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
04A	05/13/2022	ZLF	MIM	MJD	1. ADDED UPGRADEABLE PDU OPTION 2. REMOVED OBSOLETE SKU'S	P34D41M
03A	06/11/2020	CWW	MIM	JAWI	UPDATED THE OUTLET DESIGN	P34D41M
02A	06/07/2018	H.XU	MIM	JAWI	ADDED SHEET 2 WITH CONFIGURABLE PART NUMBER TABLE AND DESCRIPTION UPDATED IDENTIFICATION TO INCLUDE CONFIGURABLE OPTION 'DE-CODER'	P34D41M
01A	07/27/2017	GEORGE	MIM	EDM	INITIAL RELEASE	P34D41M

WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGN THE CLIENT SIGNATURE BOX. THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY.		SIGN
		DATE
		PRINT
TITLE INTELLIGENT SERIES PDU P34D41M-XXYZ CUSTOMER DRAWING		
ITEM REVISION NAME:		<b>PANDUIT</b>
DATASHEET FILE NAME:		
UNLESS OTHERWISE SPECIFIED DIMENSIONAL TOLERANCE ARE: mm [IN]		MATERIAL/COLOR: N/A
Tolerance(mm) 0-1<50 ±0.5 50-1<250 ±1.0 250-1<500 ±1.5 500-1<1000 ±2.5 1000-1<2000 ±4.0		DRAWING NUMBER: P34D41M_DC
DRAWN BY: GEORGE	DATE: 07/27/2017	SCALE: NONE
CHK: SEAN		SHT 1 OF 2
		SCALE: B

2 ↑ 1

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

MAIN PDU CONFIGURATIONS				
FINISHED GOOD PART NUMBER	FINISHED GOOD DESCRIPTION	COLOR	INPUT CORD LENGTH	WEIGHT
P34D41M	VERTICAL,(28) C13,(6)C19,MONITORED INPUT, 200-240V/32A/1 PHASE , TOP-END FED, 3 METER INPUT CORD, BLACK	BLACK (RAL 9005)	3M(+254MM/-127MM) 10[+10"/-5"]	6.5kg
P34D41M-BL1A	VERTICAL,(28) C13,(6)C19,MONITORED INPUT, 200-240V/32A/1 PHASE , TOP-END FED, 1 METER INPUT CORD, BLACK	BLACK (RAL 9005)	1M(+178MM/-89MM) 3.3[+3.5"/-1.75"]	5.9kg
P34D41M-RD1A	VERTICAL,(28) C13,(6)C19,MONITORED INPUT, 200-240V/32A/1 PHASE , TOP-END FED, 1 METER INPUT CORD, RED	RED (RAL 3020)	1M(+178MM/-89MM) 3.3[+3.5"/-1.75"]	5.9kg
P34D41M-RD1C	VERTICAL,(28) C13,(6)C19,MONITORED INPUT, 200-240V/32A/1 PHASE , TOP-END FED, 3 METER INPUT CORD, RED	RED (RAL 3020)	3M(+254MM/-127MM) 10[+10"/-5"]	6.5kg
P34D41M-YL1A	VERTICAL,(28) C13,(6)C19,MONITORED INPUT, 200-240V/32A/1 PHASE , TOP-END FED, 1 METER INPUT CORD, YELLOW	YELLOW (RAL 1023)	1M(+178MM/-89MM) 3.3[+3.5"/-1.75"]	5.9kg
P34D41M-YL1C	VERTICAL,(28) C13,(6)C19,MONITORED INPUT, 200-240V/32A/1 PHASE , TOP-END FED, 3 METER INPUT CORD, YELLOW	YELLOW (RAL 1023)	3M(+254MM/-127MM) 10[+10"/-5"]	6.5kg
P34D41M-BU1A	VERTICAL,(28) C13,(6)C19,MONITORED INPUT, 200-240V/32A/1 PHASE , TOP-END FED, 1 METER INPUT CORD, BLUE	BLUE (RAL 5005)	1M(+178MM/-89MM) 3.3[+3.5"/-1.75"]	5.9kg
P34D41M-BU1C	VERTICAL,(28) C13,(6)C19,MONITORED INPUT, 200-240V/32A/1 PHASE , TOP-END FED, 3 METER INPUT CORD, BLUE	BLUE (RAL 5005)	3M(+254MM/-127MM) 10[+10"/-5"]	6.5kg
P34D41M-BL2A	VERTICAL,(28) C13,(6)C19,MONITORED INPUT, 200-240V/32A/1 PHASE , BOTTOM-END FED, 1 METER INPUT CORD, BLACK	BLACK (RAL 9005)	1M(+178MM/-89MM) 3.3[+3.5"/-1.75"]	5.9kg
P34D41M-BL2C	VERTICAL,(28) C13,(6)C19,MONITORED INPUT, 200-240V/32A/1 PHASE , BOTTOM-END FED, 3 METER INPUT CORD, BLACK	BLACK (RAL 9005)	3M(+254MM/-127MM) 10[+10"/-5"]	6.5kg
P34D41M-RD2A	VERTICAL,(28) C13,(6)C19,MONITORED INPUT, 200-240V/32A/1 PHASE , BOTTOM-END FED, 1 METER INPUT CORD, RED	RED (RAL 3020)	1M(+178MM/-89MM) 3.3[+3.5"/-1.75"]	5.9kg
P34D41M-RD2C	VERTICAL,(28) C13,(6)C19,MONITORED INPUT, 200-240V/32A/1 PHASE , BOTTOM-END FED, 3 METER INPUT CORD, RED	RED (RAL 3020)	3M(+254MM/-127MM) 10[+10"/-5"]	6.5kg
P34D41M-YL2A	VERTICAL,(28) C13,(6)C19,MONITORED INPUT, 200-240V/32A/1 PHASE , BOTTOM-END FED, 1 METER INPUT CORD, YELLOW	YELLOW (RAL 1023)	1M(+178MM/-89MM) 3.3[+3.5"/-1.75"]	5.9kg
P34D41M-YL2C	VERTICAL,(28) C13,(6)C19,MONITORED INPUT, 200-240V/32A/1 PHASE , BOTTOM-END FED, 3 METER INPUT CORD, YELLOW	YELLOW (RAL 1023)	3M(+254MM/-127MM) 10[+10"/-5"]	6.5kg
P34D41M-BU2A	VERTICAL,(28) C13,(6)C19,MONITORED INPUT, 200-240V/32A/1 PHASE , BOTTOM-END FED, 1 METER INPUT CORD, BLUE	BLUE (RAL 5005)	1M(+178MM/-89MM) 3.3[+3.5"/-1.75"]	5.9kg
P34D41M-BU2C	VERTICAL,(28) C13,(6)C19,MONITORED INPUT, 200-240V/32A/1 PHASE , BOTTOM-END FED, 3 METER INPUT CORD, BLUE	BLUE (RAL 5005)	3M(+254MM/-127MM) 10[+10"/-5"]	6.5kg
UPGRADEABLE PDU CONFIGURATIONS				
FINISHED GOOD PART NUMBER	FINISHED GOOD DESCRIPTION	COLOR	INPUT CORD LENGTH	WEIGHT
P34D41U	UPGRADEABLE,VERTICAL,(28) C13,(6)C19,MONITORED INPUT, 200-240V/32A/1 PHASE , TOP-END FED, 3 METER INPUT CORD, BLACK	BLACK (RAL 9005)	3M(+254MM/-127MM) 10[+10"/-5"]	6.2kg

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
04A	05/13/2022	ZLF	MIM	MJD	1. ADDED UPGRADEABLE PDU OPTION 2. REMOVED OBSOLETE SKUs	P34D41M
03A	06/11/2020	CWW	MIM	JAWI	UPDATED THE OUTLET DESIGN	P34D41M
02A	06/07/2018	H.XU	MIM	JAWI	ADDED SHEET 2 WITH CONFIGURABLE PART NUMBER TABLE AND DESCRIPTION UPDATED IDENTIFICATION TO INCLUDE CONFIGURABLE OPTION 'DE-CODER'	P34D41M
01A	07/27/2017	GEORGE	MIM	EDM	INITIAL RELEASE	P34D41M

<p style="font-size: 8px;">WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGN THE CLIENT SIGNATURE BOX. THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY.</p>	<p style="font-size: 8px;">SIGN _____</p> <p style="font-size: 8px;">DATE _____</p> <p style="font-size: 8px;">PRINT _____</p>												
<p style="text-align: center;">TITLE <b>INTELLIGENT SERIES PDU</b> <b>P34D41M-XXYZ</b> CUSTOMER DRAWING</p>													
<p style="font-size: 8px;">ITEM REVISION NAME:</p>													
<p style="font-size: 8px;">DATASHEET FILE NAME:</p>	<p style="font-size: 8px;">MATERIAL/COLOR:  N/A</p>												
<p style="font-size: 8px;">UNLESS OTHERWISE SPECIFIED DIMENSIONAL TOLERANCE ARE: mm [IN]</p> <table style="font-size: 8px; width: 100%;"> <tr> <td style="width: 80%;">Tolerance(mm)</td> <td style="width: 20%;">±0.5</td> </tr> <tr> <td>0.4&lt;50</td> <td>±1.0</td> </tr> <tr> <td>50.4&lt;250</td> <td>±1.5</td> </tr> <tr> <td>250.4&lt;500</td> <td>±2.5</td> </tr> <tr> <td>500.4&lt;1000</td> <td>±4.0</td> </tr> <tr> <td>1000.4&lt;2000</td> <td>±4.0</td> </tr> </table>		Tolerance(mm)	±0.5	0.4<50	±1.0	50.4<250	±1.5	250.4<500	±2.5	500.4<1000	±4.0	1000.4<2000	±4.0
Tolerance(mm)	±0.5												
0.4<50	±1.0												
50.4<250	±1.5												
250.4<500	±2.5												
500.4<1000	±4.0												
1000.4<2000	±4.0												
<p style="font-size: 8px;">DRAWN BY DATE GEORGE 07/27/2017</p>	<p style="font-size: 8px;">CHK SCALE SEAN NONE</p>												
<p style="font-size: 8px;">DRAWING NUMBER: <b>P34D41M_DC</b></p>													
<p style="font-size: 8px;">SHT 2 OF 2</p>													
<p style="text-align: right;">SCALE <b>B</b></p>													

2 ↓ 1