






THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	WEIGHT
SEE SHEET 2	SEE SHEET 2



**SPECIFICATION:**


- 1. STANDARD:
  - UNIT TYPE: MONITORED INPUT
  - ORIENTATION: VERTICAL, 0U FULL
  - OUTLET QTY&TYPE: (24)C13/C15,(24)C13/C15/C19
  - INPUT VOLTAGE: 200-240VAC
  - INPUT CURRENT: 30A (24A DERATED)
  - BREAKER QTY&TYPE: (3) 20AMP, DOUBLE-POLE
  - INPUT PHASE: THREE-PHASE, DELTA
  - RATED POWER: 8.6 KVA
  - INPUT PLUG: NEMA L15-30P
  - INPUT POWER CORD: SEE SHEET 2 PART NUMBER TABLE
  - REGULATORY STANDARD: RoHS COMPLIANT
- 2. ADDITIONAL:
  - THE G6 CONTROLLER IS NOT BACKWARDS COMPATIBLE WITH ANY LEGACY CONTROLLERS
- 3. ACCESSORIES:
  - DOCUMENTATION KIT
  - PRODUCT SAFETY WARNING SHEET

**NOTES:**

1. PRIMARY DIMENSIONS ARE IN MILLIMETERS. SECONDARY DIMENSION ARE IN [ INCHES ]
2. INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE, AND LOCAL CODES
3. VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART
4. FOR FULL PRODUCT FUNCTIONALITY REFER TO USER MANUAL
5. DRAWING VIEWS SHOW THE INPUT CORD IN THE "TOP END FED" CONFIGURATION

**IDENTIFICATION**


FOR FINISHED GOOD PART NUMBER & DESCRIPTION TABLE SEE SHEET 2 CONFIGURABLE PART NUMBERS: **P48D22G-XX Y Z**




**PLUG/RECEPTACLE BLOCK**



**PLUG**  
NEMA L15-30P, 3P 4W  
30A, 120/208V MAX RATED INPUT  
24A DERATED



**RECEPTACLES**  
C13/C15 COMBO  
10A, 250V MAX RATED OUTPUT



**RECEPTACLES**  
C13/C15/C19 COMBO  
16A, 250V MAX RATED OUTPUT

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
00A	10/18/2023	NW	CSH	MJD	INITIAL RELEASE	P48D22G-XXYZ

WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGN THE CLIENT SIGNATURE BOX. THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY		SIGN
		DATE
		PRINT
TITLE <b>INTELLIGENT SERIES PDU</b> <b>P48D22G-XXYZ</b> CUSTOMER DRAWING		
ITEM REVISION NAME:		
DATASHEET FILE NAME:		
UNLESS OTHERWISE SPECIFIED DIMENSIONAL TOLERANCE ARE: mm [IN]		MATERIAL/COLOR:
Tolerance(mm) 0<L<50 ±0.5 50<L<250 ±1.0 250<L<500 ±1.5 500<L<1000 ±2.5 1000<L<2000 ±4.0		N/A
THIRD ANGLE PROJECTION		DRAWING NUMBER: <b>P48D22G-XXYZ_DC</b>
DRAWN BY NW	DATE 10/18/2023	SCALE NONE
CHK CSH	SHT 1 OF 2	
SCALE NONE		SCALE B



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

FINISHED GOOD PART NUMBER	FINISHED GOOD DESCRIPTION	COLOR	INPUT CORD LENGTH	WEIGHT
P48D22G	G6 MI PDU, 30AMP, (24) C13/C15 (24) C13/C15/C19, NEMA L15-30P-3M, TOP FED, BLACK	BLACK (RAL 9005)	3M(+254MM/-127MM) 10'[+10"/-5"]	7.7kg

B

B

A

A

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
00A	10/18/2023	NW	CSH	MJD	INITIAL RELEASE	P48D22G-XXYZ

WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGN THE CLIENT SIGNATURE BOX. THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY	SIGN	
	DATE	
	PRINT	
TITLE: INTELLIGENT SERIES PDU P48D22G-XXYZ CONTROL DRAWING		
ITEM REVISION NAME:		
DATASHEET FILE NAME:		
UNLESS OTHERWISE SPECIFIED DIMENSIONAL TOLERANCE ARE: mm [IN]		<b>PANDUIT</b>
Tolerance(mm) 0<L<50 ±0.5 50<L<250 ±1.0 250<L<500 ±1.5 500<L<1000 ±2.5 1000<L<2000 ±4.0		
THIRD ANGLE PROJECTION		MATERIAL/COLOR: N/A
DRAWN BY: NW DATE: 10/18/2023		DRAWING NUMBER: P48D22G-XXYZ_DC
CHK: CSH	SCALE: NONE	SHT 2 OF 2
		SCALE: B

