

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	WEIGHT
P24E32G-XYZ	SEE SHEET 2

SPECIFICATION:

- 1. STANDARD:**
- UNIT TYPE: SEE SHEET 2
 - ORIENTATION: VERTICAL, 0U, FULL
 - OUTLET QTY&TYPE: (12) C13, (12) C19
 - INPUT VOLTAGE: 200-240VAC
 - INPUT CURRENT: 60A (48A DERATED)
 - BREAKER QTY&TYPE: (6) 20AMP, DOUBLE-POLE
 - INPUT PHASE: THREE-PHASE DELTA
 - RATED POWER: 17.3kVA
 - INPUT PLUG: IEC 60309 3P+E 9H 60A
 - INPUT POWER CORD: SEE SHEET 2 FOR NUMBER TABLE
 - REGULATORY STANDARD: RoHS COMPLIANT






- 2. ADDITIONAL:**
- THE G6 CONTROLLER IS NOT BACKWARDS COMPATIBLE WITH ANY LEGACY CONTROLLERS

- 3. ACCESSORIES:**
- DOCUMENTATION KIT
 - PRODUCT SAFETY WARNING SHEET


- NOTES:**
- PRIMARY DIMENSIONS ARE IN MILLIMETERS. SECONDARY DIMENSION ARE IN [INCHES]
 - INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE, AND LOCAL CODES
 - VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART
 - FOR FULL PRODUCT FUNCTIONALITY REFER TO USER MANUAL
 - DRAWING VIEWS SHOW THE INPUT CORD IN THE "TOP END FED" CONFIGURATION

IDENTIFICATION
FOR FINISHED GOOD PART NUMBER & DESCRIPTION TABLE SEE SHEET 2 CONFIGURABLE PART NUMBERS: P24E32G-XX Y Z


XX: FINISHED GOOD COLOR BL=BLACK YL=YELLOW RD=RED BU=BLUE WH=WHITE GN=GREEN	Y: INPUT FEED TYPE 1=TOP-END FED 2=BOTTOM-END FED	Z: INPUT CORD LENGTH A=1 METER B=2 METER C=3 METER
--	---	---




PLUG/RECEPTACLE BLOCK



PLUG
IEC 60309, 3P 4W, 9H
IP44 (SPASHPROOF)
60A, 250V, 3-PHASE MAX RATED INPUT
48A DERATED



RECEPTACLES
IEC 60320/C19
16A, 250V MAX RATED OUTPUT



RECEPTACLES
IEC 60320/C13
10A, 250V MAX RATED OUTPUT

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
00A	08/30/2023	LWB	CSH	MJD	INITIAL RELEASE	P24E32G-XYZ

WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGN THE CLIENT SIGNATURE BOX. THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY.

SIGN: _____ DATE: _____ PRINT: _____

TITLE: INTELLIGENT SERIES PDU
P24E32G-XYZ
CUSTOMER DRAWING

ITEM REVISION NAME: _____

DATASHEET FILE NAME: _____

UNLESS OTHERWISE SPECIFIED DIMENSIONAL TOLERANCE ARE: mm [IN]
Tolerance(mm)
0<l<50 ±0.5
50<l<250 ±1.0
250<l<500 ±1.5
500<l<1000 ±2.5
1000<l<2000 ±4.0

MATERIAL/COLOR: N/A

DRAWING NUMBER: P24E32G-XYZ_DC

THIRD ANGLE PROJECTION

DRAWN BY	DATE	CHK	SCALE
LWB	08/30/2023	SEAN	NONE

SHT 1 OF 2

SCALE: B

2



1

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

FINISHED GOOD PART NUMBER	FINISHED GOOD DESCRIPTION	COLOR	INPUT CORD LENGTH	WEIGHT
P24E32G	G6 MS PDU,60AMP,(12) C13,(12) C19,IEC60309 3P 4W 9H IP44-3M,TOP FED,BLACK	BLACK (RAL 9005)	3M(+254MM/-127MM) 10' [+10"/-5"]	13.9kg

B

B



A

A

WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGN THE CLIENT SIGNATURE BOX. THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY.		SIGN										
		DATE										
		PRINT										
TITLE INTELLIGENT SERIES PDU P24E32G-XXYZ CUSTOMER DRAWING												
ITEM REVISION NAME:		PANDUIT										
DATASHEET FILE NAME:												
UNLESS OTHERWISE SPECIFIED DIMENSIONAL TOLERANCE ARE: mm [IN]		MATERIAL/COLOR: N/A										
Tolerance(mm)		DRAWING NUMBER: P24E32G-XXYZ_DC										
<table border="0"> <tr> <td>0<l<50</td> <td>±0.5</td> </tr> <tr> <td>50<l<250</td> <td>±1.0</td> </tr> <tr> <td>250<l<500</td> <td>±1.5</td> </tr> <tr> <td>500<l<1000</td> <td>±2.5</td> </tr> <tr> <td>1000<l<2000</td> <td>±4.0</td> </tr> </table>		0<l<50	±0.5	50<l<250	±1.0	250<l<500	±1.5	500<l<1000	±2.5	1000<l<2000	±4.0	
0<l<50	±0.5											
50<l<250	±1.0											
250<l<500	±1.5											
500<l<1000	±2.5											
1000<l<2000	±4.0											
THIRD ANGLE PROJECTION												
DRAWN BY	DATE	SCALE										
LWB	08/30/2023	NONE										
CHK	SCALE											
SEAN	NONE											
SHT 2 OF 2		SCALE B										

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
00A	08/30/2023	LWB	CSH	MJD	INITIAL RELEASE	P24E32G-XXYZ

2



1