



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.


PANDUIT P/N	WEIGHT
SEE SHEET 2	SEE SHEET 2



REAR VIEW



LEFT VIEW



FRONT VIEW

LEFT VIEW

SPECIFICATION:

- STANDARD
 - UNIT TYPE: BASIC
 - ORIENTATION: Horizontal (1U)
 - OUTLET QTY & TYPE: (12)C13
 - INPUT VOLTAGE: 100-240VAC
 - INPUT FREQUENCY: 50/60HZ
 - INPUT CURRENT: 16A
 - BREAKER QTY & TYPE: NONE
 - INPUT PHASE: SINGLE-PHASE
 - RATED POWER: 3.7 kVA
 - INPUT PLUG: IEC C20 100-240V Inlet
 - INPUT POWER CORD: SEE SHEET 2 PART NUMBER TABLE
 - REGULATORY STANDARD: RoHS COMPLIANT
- ADDITIONAL: NONE
- ACCESSORIES:
 - DOCUMENTATION KIT
 - PRODUCT SAFETY WARNING SHEET
 - QTY: (4) M6 X 12 PAN HEAD MACHINE SCREW
 - QTY: (4) M6 CAGE NUT

NOTES:

- PRIMARY DIMENSIONS ARE IN MILLIMETERS. SECONDARY DIMENSIONS ARE IN [INCHES]
- INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE, AND LOCAL CODES
- VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART
- FOR FULL PRODUCT FUNCTIONALITY REFER TO USER MANUAL
- DRAWING VIEWS SHOW THE INPUT CORD IN THE "TOP END FED" CONFIGURATION

IDENTIFICATION:

FOR FINISHED GOOD PART NUMBER & DESCRIPTION TABLE SEE SHEET 2 CONFIGURABLE PART NUMBERS: E12B01M-XXYZ

XX: FINISHED GOOD COLOR BL=BLACK YL=YELLOW BU=BLUE RD=RED WH=WHITE GN=GREEN	Y: INPUT FEED TYPE 1=TOP-END FED 2=BOTTOM-END FED	Z: INPUT CORD LENGTH A=1 METER B=2 METER C=3 METER
--------------------------------------------------------------------------------------	---------------------------------------------------------	-------------------------------------------------------------

PLUG / RECEPTACLE BLOCK



PLUG
IEC 60320/C20
16A, 250V MAX RATED INPUT



RECEPTACLE
IEC 60320 C13
10A, 250V MAX RATED OUTPUT

WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGN THE CLIENT SIGNATURE BOX. THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY.	SIGN
	DATE
	PRINT

TITLE	INTELLIGENT SERIES PDU E12B01M CONTROL DRAWING
-------	------------------------------------------------------

ITEM REVISION NAME:	
DATASHEET FILE NAME:	

UNLESS OTHERWISE SPECIFIED DIMENSIONAL TOLERANCE ARE: mm [IN] Tolerance (mm) 0<L≤50 ±0.5 50<L≤250 ±1.0 250<L≤500 ±1.5 500<L≤1000 ±2.5 1000<L≤2000 ±4.0	MATERIAL/COLOR: N/A
-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------	------------------------



DRAWN BY: LL DATE: 08/29/2023 CHK: MIM SCALE: NONE	DRAWING NUMBER: E12B01M_DC SHT 1 OF 2	SCALE: B
-------------------------------------------------------------	---------------------------------------------	-------------

00A	08/29/2023	LL	MIM	MJD	INITIAL RELEASE	E12B01M
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

FINISHED GOOD PART NUMBER	FINISHED GOOD DESCRIPTION	COLOR	INPUT CORD LENGTH	WEIGHT
E12B01M	BASIC PDU, 16A, (12)C13, IEC C20 INLET, BLACK	BLACK (RAL 9005)	IEC C19 TO C20 3M(+254MM/-127MM)[10'(+10"/-5"')]]	1.8kg

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
00A	08/29/2023	LL	MIM	MJD	INITIAL RELEASE	E12B01M

WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGN THE CLIENT SIGNATURE BOX. THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY.		SIGN
		DATE
		PRINT
TITLE INTELLIGENT SERIES PDU E12B01M CONTROL DRAWING		
ITEM REVISION NAME:		
DATASHEET FILE NAME:		
UNLESS OTHERWISE SPECIFIED DIMENSIONAL TOLERANCE ARE: mm [IN]		MATERIAL/COLOR:
Tolerance (mm) 0 < L ≤ 50 ±0.5 50 < L ≤ 250 ±1.0 250 < L ≤ 500 ±1.5 500 < L ≤ 1000 ±2.5 1000 < L ≤ 2000 ±4.0		N/A
 THIRD ANGLE PROJECTION		DRAWING NUMBER:
DRAWN BY: LL DATE: 08/29/2023 CHK: MIM SCALE: NONE		E12B01M_DC SHT 2 OF 2
		SCALE: B