

18900 Panduit Drive Tinley Park, IL 60487

Customer Service: 800-777-3300

TDS: Effective Date: Revision:

GMDU 27OCT2021

Detectable Underground Tape

This specification is intended to outline the physical and chemical properties of PANDUIT's detectable underground tape and include the following part numbers and printable material identifiers:

Part Number Prefixes			
HTDU*			
GHTDU*			

Printable Material Suffixes		

PRODUCT SPECIFICATIONS:

Description: GMDU is a detectable tape consisting of a 0.35 mil solid aluminum core encased in a protective plastic jacket. Tape shall be detectable up to a depth of 18 to 24 inches for a 3 inch wide tape and 24 to 30 inches for a 6 inch wide tape.

Standard Colors: Orange, red and blue

Thickness: 4.5 to 6.5 mils thick (complete laminate structure (core, films, and inks)

PROPERTIES: PERFORMANCE:

MD: 18 lb/in width (22.6 MPa) minimum (ASTM D-882) Tensile Strength:

MD: 50% minimum Elongation:

Material density is 1.090 gm/cc minimum (ASTM D792-66). Core density will Density:

vary depending on moisture conditions.

Resistance to Acids: Resists acids of 4.0 pH for a minimum of 10 years duration Resistance to Bases: Resists bases of 10.0 pH for a minimum of 10 years duration

Elevated Temperature Exposure: After 8 hours at 220°F (104°C) there was no deterioration of the material

ASTM: American Society for Testing and Materials (U.S.A.)

LIMITED WARRANTY

All PANDUIT Identification Solution Products (except for Software programs) are warranted to be free from defects in material and workmanship at the time of sale but our obligation under this warranty is limited to replacement of the product proved to be defective within 6 months from the date of sale, or in the case of printers, within 90 days from the date of sale. This warranty is void if the products or printers are modified, altered or misused in any way. Use of PANDUIT printers with any product other than the specified PANDUIT products for which the printer was designed constitutes misuse. Before using, the user shall determine the suitability of the product for its intended use and user assumes all risk and liability whatsoever in connection therewith. The foregoing may not be altered except by an agreement signed by officers or seller and manufacturer.

NEITHER PANDUIT OR SELLER SHALL BE LIABLE FOR ANY OTHER INJURY, LOSS OR DAMAGE, WHETHER DIRECT OR CONSEQUENTIAL, ARISING OUT OF THE USE OF, OR THE INABILITY TO USE THE PRODUCT OR THE PRINTER.

THIS WARRANTY IS MADE IN LIEU OF AND EXCLUDES ALL OTHER WARRANTIES, EXPRESS OR IMPLIED. THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS OF PARTICULAR USE ARE SPECIFICALLY EXCLUDED.

The information contained in this literature is based on our experience to date and is believed to be reliable. It is intended as a guide or use by persons having technical skill at their own discretion and risk. We do not guarantee favorable results or assume any liability in connection with its use. Dimensions contained herein are for reference purposes only. This publication is not to be taken as a license to operate under, or a recommendation to infringe any existing patents. This supersedes and voids all previous literature, etc.

Page 1 of 1 © 2021 PANDUIT Corp

TDS: GMDU