



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

NOTES:

1. VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A LIST OF CURRENT PARTS APPLICABLE USE WITH THIS PRODUCT.
2. PRODUCT IS REMOVED THE USB TYPE "A" FEMALE PORT USING THE SMARTKEEPER MASTER KEY (PANDUIT P.N.: SKMKEY).
3. SEE INSTALLATION INSTRUCTION FOR PROPER USE OF PRODUCT.
4. PARTS INCLUDES (DESCRIPTION: MATERIAL/COLOR):
 - 4A. USB TYPE "A" INTERNAL BODY WITH UNIQUE FEMALE KEYED PATTERN: POLY OXY METHYLENE (POM), FLAME RATING: UL94 HB/RED.
 - 4B. SHIELD: BRASS STEEL/NICKEL PLATING.
5. PRODUCT IS DESIGNED FOR INDOOR USE ONLY.
6. OPERATING TEMPERATURE AND HUMIDITY RANGE:
 - 6A. TEMPERATURE RANGE: -4°F (-20°C) TO +140°F (+60°C)
 - 6B. HUMIDITY RANGE: 10-70% NON-CONDENSING RELATIVE HUMIDITY.
7. STORAGE CONDITIONS:
 - 7A. TEMPERATURE RANGE: -4°F (-20°C) TO +176°F (+80°)
 - 7B. HUMIDITY RANGE: 10-80% NON-CONDENSING RELATIVE HUMIDITY.
8. WEIGHT: 0.02 LBS/ (10) PCS [10.0 grams/ (10) PCS].
9. DIMENSIONS IN [] ARE METRIC.
10. ALL MATERIALS AND COMPONENTS USED MEET THE MATERIALS RESTRICTIONS OF RoHs, (EUROPEAN DIRECTIVE 2011/65/EU ON THE RESTRICTION OF HAZARDOUS SUBSTANCES) AS PROPOSED BY THE RoHs TECHNICAL ADAPTATION COMMITTEE.



PART NUMBER		SKUSBA - V	
TITLE		SMARTKEEPER USB TYPE "A" BLOCKOUT DEVICE	
ITEM REVISION NAME		CUSTOMER DRAWING	
DATASET FILE NAME		00402NAB/01	
MATERIAL		SEE NOTES	
DRAWING NUMBER		00402NAB - DC	
DRAWN BY		MDJR	
DATE		04-25-19	
CHK		DCS	
SCALE		2:1	
SHEET 1 OF 1		A	

01A	10-20-22	MDJR	JCO	REFR	UPDATED VIEWS	00402NAB-DC
00A	04-25-19	MDJR	DCS	MMR	DRAWING RELEASED	00402NAB-DC
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN

A-SIZE CUSTOMER