


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

NOTES:

- \*1. REFER TO [www.panduit.com](http://www.panduit.com) FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE AND PART COLOR
2. SPLICING MAY OCCUR FOR ROLL SIZES LONGER THAN 10 FT.
3. REVERSE CUT.
4. SOME GAP WILL BE PRESENT BETWEEN WINDS
5. ALL MATERIALS AND COMPONENTS USED MEET THE MATERIAL RESTRICTIONS OF RoHS EUROPEAN DIRECTIVE ON THE RESTRICTION OF HAZARDOUS SUBSTANCES AS PROPOSED BY THE RoHS TECHNICAL ADAPTATION COMMITTEE.
6. DIMENSIONS IN [ ] ARE METRIC.

*PANDUIT PART NUMBER	A IN [mm]	B IN [mm]	T IN [mm]	WEIGHT LBS (g)/ 100 FT
T12FR	.125 [3.2]	.218 ±.047 [5.5 ±1.2]	.030 ±.006 [0.8 ±0.2]	0.6 (250)
T19FR	.188 [4.8]	.250 ±.047 [6.4 ±1.2]	.035 ±.008 [0.9 ±0.2]	1.1 (500)
T25FR	.250 [6.4]	.375 ±.047 [9.5 ±1.2]	.040 ±.008 [1.0 ±0.2]	1.6 (750)
T38FR	.375 [9.5]	.437 ±.047 [11.1 ±1.2]	.055 ±.010 [1.4 ±0.3]	3.5 (1600)
T50FR	.500 [12.7]	.500 ±.047 [12.7 ±1.2]	.060 ±.016 [1.5 ±0.4]	5.2 (2350)
T62FR	.625 [15.9]	.625 ±.047 [15.9 ±1.2]	.062 ±.020 [1.6 ±0.5]	6.8 (3100)
T75FR	.750 [19.1]	.875 ±.047 [22.2 ±1.2]	.065 ±.020 [1.7 ±0.5]	8.7 (3950)
T100FR	1.000 [25.4]	1.125 ±.047 [28.6 ±1.2]	.070 ±.020 [1.8 ±0.5]	12.8 (5800)



PART NUMBER					SEE TABLE																		
TITLE										FLAME RETARDANT POLYETHYLENE SPIRAL WRAP													
CUSTOMER DRAWING																							
ITEM REVISION NAME					03903NBD/00																		
DATASET FILE NAME					03903NBD_DC/00A																		
					THIRD ANGLE PROJECTION																		
MATERIAL					POLYETHYLENE					DRAWING NUMBER					03903NBD - DC								
DRAWN BY		DATE		CHK		SCALE		SHEET 1 OF 1		REV		DATE		BY		CHK		APR		DESCRIPTION		ECN	
KLN		06/19/2024		MSAD		NONE				00A		06/19/2024		KLN		SEWH		MSAD		INITIAL RELEASE		GAECN07143/00	

A-SIZE CUSTOMER