





THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	WEIGHT
SEE SHEET 2	SEE SHEET 2



SPECIFICATION:

1. STANDARD


UNIT TYPE:	MONITORED SWITCHED
ORIENTATION:	VERTICAL, MID
OUTLET QTY & TYPE:	(18) 5-20R
INPUT VOLTAGE:	100-120VAC
INPUT CURRENT:	30A (24A DERATED)
BREAKER QTY & TYPE:	(2) 20AMP, SINGLE-POLE
INPUT PHASE:	SINGLE-PHASE
RATED POWER:	2.9 kVA
INPUT PLUG:	NEMA L5-30P
INPUT POWER CORD:	SEE TABLE SHEET 2
REGULATORY STANDARD:	RoHS COMPLIANT
2. ADDITIONAL:
 - THE G6 CONTROLLER IS NOT BACKWARDS COMPATIBLE WITH ANY LEGACY CONTROLLERS
3. ACCESSORIES:
 - DOCUMENTATION KIT
 - PRODUCT SAFETY WARNING SHEET

NOTES:


1. PRIMARY DIMENSIONS ARE IN MILLIMETERS. SECONDARY DIMENSION ARE IN [INCHES]
2. INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE, AND LOCAL CODES
3. VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART
4. FOR FULL PRODUCT FUNCTIONALITY REFER TO USER MANUAL
5. DRAWING VIEWS SHOW THE INPUT CORD IN THE "TOP END FED" CONFIGURATION

IDENTIFICATION

FOR FINISHED GOOD PART NUMBER & DESCRIPTION TABLE SEE SHEET 2 CONFIGURABLE PART NUMBERS: P18E23G-XX Y Z



20 AMP, SINGLE-POLE ELECTRO MECHANICAL SWITCH / BREAKER (2) PLACES



REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
00A	10/08/2023	NW	CSH	MJD	INITIAL RELEASE	P18E23G-XXXYZ

WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGN THE CLIENT SIGNATURE BOX. THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY		SIGN
		DATE
		PRINT
TITLE INTELLIGENT SERIES PDU P18E23G-XXXXYZ CUSTOMER DRAWING		
ITEM REVISION NAME		<h1>PANDUIT</h1>
DATASHEET FILE NAME:		
UNLESS OTHERWISE SPECIFIED DIMENSIONAL TOLERANCE ARE: mm [IN]		
Tolerance(mm) 0xL<50 ±0.5 50xL<250 ±1.0 250xL<500 ±1.5 500xL<1000 ±2.5 1000xL<2000 ±4.0		
THIRD ANGLE PROJECTION		MATERIAL/COLOR: N/A
DRAWN BY DATE		DRAWING NUMBER: P18E23G-XXXXYZ_DC
NW	09/06/2023	SCALE: NONE
CHK	CSH	SHT 1 OF 2
		SCALE: B

2

1

2

1

2



1

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

FINISHED GOOD PART NUMBER	FINISHED GOOD DESCRIPTION	COLOR	INPUT CORD LENGTH	WEIGHT
P18E23G	G6 MS PDU, 30AMP, (18) 5-20R, NEMA L5-30P-3M, TOP FED, BLACK	BLACK (RAL 9005)	3M(+254MM-127MM) 10' [+10"/-5"]	7.9kg


B

B

A

A

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
00A	10/08/2023	NW	CSH	MJD	INITIAL RELEASE	P18E23G-XXXXZ

WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGN THE CLIENT SIGNATURE BOX. THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY		SIGN
		DATE
		PRINT
TITLE INTELLIGENT SERIES PDU P18E23G-XXXXZ CUSTOMER DRAWING		
ITEM REVISION NAME:		
DATASHEET FILE NAME:		
UNLESS OTHERWISE SPECIFIED DIMENSIONAL TOLERANCE ARE: mm [IN]		MATERIAL/COLOR:
 THIRD ANGLE PROJECTION Tolerance(mm) 0<L<50 ±0.5 50<L<250 ±1.0 250<L<500 ±1.5 500<L<1000 ±2.5 1000<L<2000 ±4.0		N/A
DRAWN BY: NW		DRAWING NUMBER: P18E23G-XXXXZ_DC
DATE: 09/06/2023	CHK: CSH	SCALE: NONE
SHT 2 OF 2		SCALE: B

2



1