

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	WEIGHT
SEE SHEET 2	SEE SHEET 2

**SPECIFICATION:**


- STANDARD  
 UNIT TYPE: MONITORED PER OUTLET  
 ORIENTATION: VERTICAL, 0U FULL  
 OUTLET QTY & TYPE: (18)C13, (6)C19  
 INPUT VOLTAGE: 200-240/346-415VAC  
 INPUT FREQUENCY: 50/60HZ  
 INPUT CURRENT: 32A  
 BREAKER QTY & TYPE: (6)16AMP, SINGLE-POLE  
 INPUT PHASE: THREE-PHASE(WYE)  
 RATED POWER: 22 kVA  
 INPUT PLUG: IEC 60309 3P+N+E 6H 32A  
 INPUT POWER CORD: SEE SHEET 2 PART NUMBER TABLE  
 REGULATORY STANDARD: RoHS COMPLIANT
- ADDITIONAL:  
 NONE
- ACCESSORIES:  
 DOCUMENTATION KIT  
 PRODUCT SAFETY WARNING SHEET

**NOTES:**

- PRIMARY DIMENSIONS ARE IN MILLIMETERS. SECONDARY DIMENSIONS ARE IN [INCHES]
- INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE, AND LOCAL CODES
- VISIT OUR ON-LINE CATALOG AT [WWW.PANDUIT.COM](http://WWW.PANDUIT.COM) FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART
- FOR FULL PRODUCT FUNCTIONALITY REFER TO USER MANUAL
- DRAWING VIEWS SHOW THE INPUT CORD IN THE "TOP END FED" CONFIGURATION

**IDENTIFICATION:**

FOR FINISHED GOOD PART NUMBER & DESCRIPTION TABLE SEE SHEET 2 CONFIGURABLE PART NUMBERS: E24F08M-XXYZ




WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGN THE CLIENT SIGNATURE BOX. THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY.


SIGN \_\_\_\_\_  
 DATE \_\_\_\_\_  
 PRINT \_\_\_\_\_

TITLE		INTELLIGENT SERIES PDU E24F08M CONTROL DRAWING	
ITEM REVISION NAME:		<b>PANDUIT</b>	
DATASHEET FILE NAME:			
UNLESS OTHERWISE SPECIFIED DIMENSIONAL TOLERANCE ARE: mm [IN]		MATERIAL/COLOR: N/A	
Tolerance (mm)		DRAWING NUMBER: E24F08M_DC	
THIRD ANGLE PROJECTION		SHT 1 OF 2	
DRAWN BY	DATE	CHK	SCALE
LL	08/29/2023	MIM	NONE
SCALE		SCALE	
NONE		B	


**LEFT VIEW**



**REAR VIEW**




**RIGHT VIEW**



**FRONT VIEW**


**BOTTOM VIEW**



**PLUG / RECEPTACLE BLOCK**



**PLUG**  
 IEC 60309 3P+N+E 6H  
 IP44 (SPLASHPROOF)  
 32A, 346-415V MAX RATED INPUT



**RECEPTACLE**  
 IEC 60320 C13  
 10A, 250V MAX RATED OUTPUT





**RECEPTACLE**  
 IEC 60320 C19  
 16A, 250V MAX RATED OUTPUT

00A	08/29/2023	LL	MIM	MJD	INITIAL RELEASE	E24F08M
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

FINISHED GOOD PART NUMBER	FINISHED GOOD DESCRIPTION	COLOR	INPUT CORD LENGTH	WEIGHT
E24F08M	MPO PDU, 32A, (18)C13 (6)C19, IEC 60309 3P+N+E 6h IP44-3M, TOP-FED, BLACK	BLACK(RAL 9005)	3M(+254MM/-127MM)[10'(+10"/-5")]	8.6kg

WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGN THE CLIENT SIGNATURE BOX. THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY.		SIGN
		DATE
		PRINT
TITLE <b>INTELLIGENT SERIES PDU E24F08M</b> CONTROL DRAWING		
ITEM REVISION NAME:		
DATASHEET FILE NAME:		
UNLESS OTHERWISE SPECIFIED DIMENSIONAL TOLERANCE ARE: mm [IN]		MATERIAL/COLOR:
Tolerance (mm) 0 < L ≤ 50 ± 0.5 50 < L ≤ 250 ± 1.0 250 < L ≤ 500 ± 1.5 500 < L ≤ 1000 ± 2.5 1000 < L ≤ 2000 ± 4.0		N/A
 THIRD ANGLE PROJECTION		DRAWING NUMBER:
DRAWN BY: LL    DATE: 08/29/2023    CHK: MIM    SCALE: NONE		<b>E24F08M_DC</b>
		SHT 1 OF 2
		SCALE: <b>B</b>

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
00A	08/29/2023	LL	MIM	MJD	INITIAL RELEASE	E24F08M