





THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	WEIGHT
SEE SHEET 2	SEE SHEET 2



SPECIFICATION:

1. STANDARD:
 UNIT TYPE: MONITORED & SWITCHED PER OUTLET
 ORIENTATION: VERTICAL, 0U FULL
 OUTLET QTY&TYPE: (21) C13/C15, (21) C13/C15/C19
 INPUT VOLTAGE: 200-240/346-415VAC
 INPUT CURRENT: 60A (48A DERATED) (NA) / 63A (EU)
 BREAKER QTY&TYPE: (12) 20AMP, SINGLE-POLE
 INPUT PHASE: THREE-PHASE, WYE
 RATED POWER: DUAL-RATED: 34.6kVA (NA) / 43.5kVA (EU)
 INPUT PLUG: IEC 60309, 3P+N+E (IP44)
 INPUT POWER CORD: SEE SHEET 2 PART NUMBER TABLE
 REGULATORY STANDARD: RoHS COMPLIANT

2. ADDITIONAL:
 THE G6 CONTROLLER IS NOT BACKWARDS COMPATIBLE WITH ANY LEGACY CONTROLLERS
 CIRCUIT BREAKER TO BE RATED AT 10KAIC

3. ACCESSORIES:
 DOCUMENTATION KIT
 PRODUCT SAFETY WARNING SHEET

NOTES:
 1. PRIMARY DIMENSIONS ARE IN MILLIMETERS. SECONDARY DIMENSION ARE IN [INCHES]
 2. INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE, AND LOCAL CODES
 3. VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART
 4. FOR FULL PRODUCT FUNCTIONALITY REFER TO USER MANUAL
 5. DRAWING VIEWS SHOW THE INPUT CORD IN THE "TOP END FED" CONFIGURATION


IDENTIFICATION
 FOR FINISHED GOOD PART NUMBER & DESCRIPTION TABLE SEE SHEET 2 CONFIGURABLE PART NUMBERS: **P42G21G-XX Y Z**

XX: FINISHED GOOD COLOR BL =BLACK RD =RED WH =WHITE YL =YELLOW BU =BLUE GN =GREEN	Y: INPUT FEED TYPE 1 =TOP-END FED 2 =BOTTOM-END FED	Z: INPUT CORD LENGTH A =1 METER B =2 METER C =3 METER
--	--	---


PLUG/RECEPTACLE BLOCK



PLUG
 IEC 60309, 4P 5W,6H
 IP44(SPLASHPROOF)
 60A(48A DERATED)/63A
 346-415V MAX RATED INPUT



RECEPTACLES
 C13/C15 COMBO
 10A, 250V MAX RATED OUTPUT



RECEPTACLES
 C13/C15/C19 COMBO
 16A, 250V MAX RATED OUTPUT

00A	11/03/2023	NW	CSH	MJD	INITIAL RELEASE	P42G21G-XXYZ			
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN			

WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGN THE CLIENT SIGNATURE BOX. THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY	SIGN DATE PRINT
TITLE INTELLIGENT SERIES PDU P42G21G-XXYZ CUSTOMER DRAWING	
ITEM REVISION NAME: DATASHEET FILE NAME:	PANDUIT
UNLESS OTHERWISE SPECIFIED DIMENSIONAL TOLERANCE ARE: mm [IN] Tolerance(mm) 0<L<50 ±0.5 50<L<250 ±1.0 250<L<500 ±1.5 500<L<1000 ±2.5 1000<L<2000 ±4.0	
THIRD ANGLE PROJECTION	DRAWING NUMBER: P42G21G-XXYZ_DC
DRAWN BY: NW DATE: 11/03/2023 CHK: CSH SCALE: NONE	SHT 1 OF 2 SCALE: B

2



1

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

FINISHED GOOD PART NUMBER	FINISHED GOOD DESCRIPTION	COLOR	INPUT CORD LENGTH	WEIGHT
P42G21G	G6 MSPO PDU, 63AMP, (21) C13/C15 (21) C13/C15/C19, IEC 60309 4P 5W 6H IP44-3M, TOP FED, BLACK	BLACK (RAL 9005)	3M(+254MM/-127MM) 10' [+10"/-5"]	12.7kg

B

B

A

A

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
00A	11/03/2023	NW	CSH	MJD	INITIAL RELEASE	P42G21G-XXYZ

WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGN THE CLIENT SIGNATURE BOX. THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY	SIGN	
	DATE	
	PRINT	
TITLE		INTELLIGENT SERIES PDU P42G21G-XXYZ CUSTOMER DRAWING
ITEM REVISION NAME:		
DATASHEET FILE NAME:		
UNLESS OTHERWISE SPECIFIED DIMENSIONAL TOLERANCE ARE: mm [IN]		PANDUIT MATERIAL/COLOR: N/A
THIRD ANGLE PROJECTION		
Tolerance(mm) 0<L<50 ±0.5 50<L<250 ±1.0 250<L<500 ±1.5 500<L<1000 ±2.5 1000<L<2000 ±4.0		DRAWING NUMBER: P42G21G-XXYZ_DC
DRAWN BY	DATE	SCALE
NW	11/03/2023	NONE
CHK		
CSH		
SHT 2 OF 2		SCALE B

2



1