



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.


PANDUIT P/N	WEIGHT
P24E29G-XXYZ	SEE SHEET 2




LEFT VIEW



REAR VIEW



RIGHT VIEW



FRONT VIEW

SPECIFICATION:

1. STANDARD:

UNIT TYPE:	MONITORED SWITCHED
ORIENTATION:	VERTICAL, 0U, FULL
OUTLET QTY&TYPE:	(18) C13, (6) C19
INPUT VOLTAGE:	200-240VAC
INPUT CURRENT:	30A (24A DERATED)
BREAKER QTY&TYPE:	(3) 20AMP, DOUBLE-POLE
INPUT PHASE:	THREE-PHASE DELTA
RATED POWER:	8.6kVA
INPUT PLUG:	NEMA L15-30P
INPUT POWER CORD:	SEE SHEET 2 FOR PART NUMBER TABLE
REGULATORY STANDARD:	RoHS COMPLIANT

2. ADDITIONAL:

THE G6 CONTROLLER IS NOT BACKWARDS COMPATIBLE WITH ANY LEGACY CONTROLLERS

3. ACCESSORIES:


DOCUMENTATION KIT
PRODUCT SAFETY WARNING SHEET

NOTES:

- PRIMARY DIMENSIONS ARE IN MILLIMETERS. SECONDARY DIMENSION ARE IN [INCHES]
- INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE, AND LOCAL CODES
- VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART
- FOR FULL PRODUCT FUNCTIONALITY REFER TO USER MANUAL
- DRAWING VIEWS SHOW THE INPUT CORD IN THE "TOP END FED" CONFIGURATION

IDENTIFICATION

FOR FINISHED GOOD PART NUMBER & DESCRIPTION TABLE SEE SHEET 2 CONFIGURABLE PART NUMBERS: **P24E29G-XX Y Z**




BOTTOM VIEW

XX: FINISHED GOOD COLOR BL=BLACK RD=RED WH=WHITE YL=YELLOW BU=BLUE GN=GREEN	Y: INPUT FEED TYPE 1=TOP-END FED 2=BOTTOM-END FED	Z: INPUT CORD LENGTH A=1 METER B=2 METER C=3 METER
---	---	---


PLUG/RECEPTACLE BLOCK



PLUG
NEMA L15-30P, 3P 4W
30A, 250V, 3-PHASE MAX RATED INPUT
24A DERATED



RECEPTACLES
IEC 60320/C19
16A, 250V MAX RATED OUTPUT



RECEPTACLES
IEC 60320/C13
10A, 250V MAX RATED OUTPUT

					INITIAL RELEASE		P24E29G-XXYZ	
00A	10/11/2023	LWB	CSH	MJD				
REV	DATE	BY	CHK	APR		DESCRIPTION	ECN	

WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGN THE CLIENT SIGNATURE BOX. THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY.

SIGN: _____ DATE: _____ PRINT: _____

TITLE: INTELLIGENT SERIES PDU P24E29G-XXYZ
CUSTOMER DRAWING

ITEM REVISION NAME: _____
DATASHEET FILE NAME: _____

UNLESS OTHERWISE SPECIFIED
DIMENSIONAL TOLERANCES ARE: mm [IN]

Tolerance(mm)	
0.4<50	±0.5
50.4<250	±1.0
250.4<500	±1.5
500.4<1000	±2.5
1000.4<2000	±4.0

MATERIAL/COLOR: N/A

DRAWING NUMBER: P24E29G-XXYZ_DC

THIRD ANGLE PROJECTION

DRAWN BY: LWB DATE: 10/11/2023 CHK: SEAN SCALE: NONE

SHIT 1 OF 2 SCALE: B

2



1

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

FINISHED GOOD PART NUMBER	FINISHED GOOD DESCRIPTION	COLOR	INPUT CORD LENGTH	WEIGHT
P24E29G	G6 MS PDU,30AMP,(18) C13,(6) C19,NEMA L15-30P-3M, TOP FED, BLACK	BLACK (RAL 9005)	3M(+254MM-127MM) 10' [+10"/-5"]	9.4kg

B

B



A

A

WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGN THE CLIENT SIGNATURE BOX. THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY		SIGN																		
		DATE																		
		PRINT																		
TITLE INTELLIGENT SERIES PDU P24E29G-XXYZ CUSTOMER DRAWING																				
ITEM REVISION NAME:		PANDUIT																		
DATASHEET FILE NAME:																				
UNLESS OTHERWISE SPECIFIED DIMENSIONAL TOLERANCE ARE: mm [IN]		MATERIAL/COLOR: N/A																		
<table border="0"> <tr> <td></td> <td>Tolerance(mm)</td> <td></td> </tr> <tr> <td>0<L<50</td> <td>±0.5</td> <td></td> </tr> <tr> <td>50<L<250</td> <td>±1.0</td> <td></td> </tr> <tr> <td>250<L<500</td> <td>±1.5</td> <td></td> </tr> <tr> <td>500<L<1000</td> <td>±2.5</td> <td></td> </tr> <tr> <td>1000<L<2000</td> <td>±4.0</td> <td></td> </tr> </table>			Tolerance(mm)		0<L<50	±0.5		50<L<250	±1.0		250<L<500	±1.5		500<L<1000	±2.5		1000<L<2000	±4.0		DRAWING NUMBER: P24E29G-XXYZ_DC
	Tolerance(mm)																			
0<L<50	±0.5																			
50<L<250	±1.0																			
250<L<500	±1.5																			
500<L<1000	±2.5																			
1000<L<2000	±4.0																			
DRAWN BY	DATE	SCALE																		
LWB	10/11/2023	NONE																		
CHK	SCALE																			
SEAN	NONE																			
SHT 2 OF 2		SCALE B																		

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
00A	10/11/2023	LWB	CSH	MJD	INITIAL RELEASE	P24E29G-XXYZ

2



1