


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

NOTES:

- *1. REFER TO www.panduit.com FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE AND PART COLOR
- 2. SPLICING MAY OCCUR FOR ROLL SIZES LONGER THAN 10 FT.
- 3. REVERSE CUT.
- 4. SOME GAP WILL BE PRESENT BETWEEN WINDS
- 5. ALL MATERIALS AND COMPONENTS USED MEET THE MATERIAL RESTRICTIONS OF RoHS EUROPEAN DIRECTIVE ON THE RESTRICTION OF HAZARDOUS SUBSTANCES AS PROPOSED BY THE RoHS TECHNICAL ADAPTATION COMMITTEE.
- 6. DIMENSIONS IN [] ARE METRIC.

*PANDUIT PART NUMBER	A IN [mm]	B IN [mm]	T IN [mm]	WEIGHT LBS (g)/ 100 FT
T12N	.125 [3.2]	.218 ±.047 [5.5 ±1.2]	.015 ±.004 [0.4 ±0.1]	0.3 (150)
T19N	.188 [4.8]	.250 ±.047 [6.4 ±1.2]	.020 ±.008 [0.5 ±0.2]	0.5 (250)
T25N	.250 [6.4]	.375 ±.047 [9.5 ±1.2]	.023 ±.008 [0.6 ±0.2]	0.8 (350)
T38N	.375 [9.5]	.437 ±.047 [11.1 ±1.2]	.030 ±.010 [0.8 ±0.3]	1.6 (750)
T50N	.500 [12.7]	.500 ±.047 [12.7 ±1.2]	.032 ±.012 [0.8 ±0.3]	2.3 (1050)
T62N	.625 [15.9]	.625 ±.047 [15.9 ±1.2]	.035 ±.020 [0.9 ±0.5]	3.2 (1450)
T75N	.750 [19.1]	.875 ±.047 [22.2 ±1.2]	.040 ±.020 [1.0 ±0.5]	4.4 (2000)
T100N	1.000 [25.4]	1.125 ±.047 [28.6 ±1.2]	.045 ±.020 [1.1 ±0.5]	6.6 (3000)



PART NUMBER					SEE TABLE										
TITLE										NYLON SPIRAL WRAP					
										CUSTOMER DRAWING					
ITEM REVISION NAME					03903NBF/00										
DATASET FILE NAME					03903NBF_DC/00A										
MATERIAL					NYLON 6										
DRAWN BY					DATE		CHK		SCALE		DRAWING NUMBER				
KLN		06/19/2024			MSAD		NONE			03903NBF - DC					
REV					DESCRIPTION					SHEET 1 OF 1					
00A					INITIAL RELEASE					A					
06/19/2024					GAECN07145/00										

A-SIZE CUSTOMER