



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.


PANDUIT P/N	WEIGHT
P36G31M-XXYZ	SEE SHEET 2




LEFT VIEW




REAR VIEW



RIGHT VIEW



FRONT VIEW



BOTTOM VIEW

SPECIFICATION:

- STANDARD
 - UNIT TYPE: MONITORED & SWITCHED PER OUTLET
 - ORIENTATION: VERTICAL, 0U FULL
 - OUTLET QTY & TYPE: (24)C13, (12)C19
 - INPUT VOLTAGE: 200-240VAC
 - INPUT CURRENT: 60A (48A DERATED)
 - BREAKER QTY & TYPE: (6) 20A, DOUBLE-POLE
 - INPUT PHASE: THREE-PHASE (DELTA)
 - RATED POWER: 17.3 kVA
 - INPUT PLUG: SEE TABLE SHEET 2
 - INPUT POWER CORD: SEE TABLE SHEET 2
 - REGULATORY STANDARD: RoHS COMPLIANT
- ADDITIONAL:
 - OUTLET CONTROL RELAY: NORMALLY OPEN 80 AMP INRUSH
- ACCESSORIES:
 - (1) QUICK-START GUIDE

NOTES:


- PRIMARY DIMENSIONS ARE IN MILLIMETERS. SECONDARY DIMENSIONS ARE IN [INCHES]
- INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE, AND LOCAL CODES
- VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PRODUCT
- FOR FULL PRODUCT FUNCTIONALITY REFER TO USER MANUAL
- DRAWING VIEWS SHOW THE INPUT CORD IN THE "TOP END FED" CONFIGURATION

IDENTIFICATION


FOR FINISHED GOOD PART NUMBER & DESCRIPTION TABLE SEE SHEET 2 CONFIGURABLE PART NUMBERS: P36G31M-XXYZ

XX: FINISHED GOOD COLOR BL = BLACK YL =YELLOW RD =RED BU =BLUE WH =WHITE GN =GREEN	Y: INPUT FEED TYPE 1 =TOP-END FED 2 =BOTTOM-END FED	Z: INPUT CORD LENGTH A =1 METER B =2 METER C =3 METER
---	---	--

PLUG / RECEPTACLE BLOCK



PLUG
IEC 60309, 3P 4W, 9H
IP44 (SPASHPROOF)
60A, 250VAC MAX RATED INPUT
(48A DERATED)



RECEPTACLE
IEC 60320 C13
10A, 250V MAX RATED OUTPUT



RECEPTACLE
IEC 60320 C19
16A, 250V MAX RATED OUTPUT

WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGN THE CLIENT SIGNATURE BOX. THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY.

SIGN _____
DATE _____
PRINT _____

TITLE
INTELLIGENT SERIES PDU
P36G31M-XXYZ
CUSTOMER DRAWING

ITEM REVISION NAME
DATASET FILE NAME



UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: m m [IN]
Tolerance (mm)
0-<L≤50 ±0.5
50-<L≤250 ±1.0
250-<L≤500 ±1.5
500-<L≤1000 ±2.5
1000-<L≤2000 ±4.0

MATERIAL:
N/A
DRAWING NUMBER:
P36G31M_DC

REV.	DATE	BY	CHK	APR	DESCRIPTION	ECN
REV01A	10/28/2021	WAC	PJST	MJD	INITIAL DC RELEASE	P36G31M
REVISIONS						

BY	DATE	CHK	SCALE	SHEET 1 OF 2	SIZE
WAC	10/26/2021	-	NTS		B

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



FINISHED GOOD PART NUMBER	FINISHED GOOD DESCRIPTION	COLOR	INPUT CORD LENGTH	WEIGHT
P36G31M	MSPO PDU, 60AMP, (24)C13, (12)C19, IEC 60309 3P+E 9H-3M, TOP FED, BLACK	BLACK (9005)	3M (+254MM / -127MM) [10'(+10"/-5")]	12.2kg

B

B

A

A

REV.	DATE	BY	CHK	APR	DESCRIPTION	ECN
REV01A	10/28/2021	WAC	PJST	MJD	INITIAL DC RELEASE	P36G31M
REVISIONS						

WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGN THE CLIENT SIGNATURE BOX. THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY.

SIGN _____
DATE _____
PRINT _____

TITLE
INTELLIGENT SERIES PDU
P36G31M-XXYZ
CUSTOMER DRAWING

ITEM REVISION NAME _____
DATASET FILE NAME _____

UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: m m [IN]

	Tolerance (mm)	
0<L≤50	±0.5	
50<L≤250	±1.0	
250<L≤500	±1.5	
500<L≤1000	±2.5	
1000<L≤2000	±4.0	

MATERIAL: **N/A**

DRAWING NUMBER: **P36G31M_DC**

BY: **WAC** DATE: **10/26/2021** CHK: **-** SCALE: **NTS**

SHEET 2 OF 2 SIZE **B**

