

Safety Data Sheet

Issue Date: 28-Apr-2014 Revision Date: 16-Dec-2019 Version 1

1. IDENTIFICATION

Product Identifier

Product Name Duct Seal

Other means of identification

SDS # PAN-003

Product Code DS1 and DS5

Recommended use of the chemical and restrictions on use

Recommended Use Duct sealant.

Details of the supplier of the safety data sheet

Supplier AddressAustralian ImporterPanduitPanduit International Ltd.,18900 Panduit Dr.30-36 Kitchen Road

Tinley Park, IL 60487 Dandenong, Victoria, 3175 Australia

Emergency Telephone Number

Company Phone Number Phone: 708-532-1800

Fax: 708-532-1811

Emergency Telephone (24 hr) INFOTRAC 1-352-323-3500 (International)

1-800-535-5053 (North America)

2. HAZARDS IDENTIFICATION

Appearance Dark gray-green soft solid Physical State Semi-solid Odor Slight characteristic odor

Classification

Carcinogenicity Category 1A

Hazards Not Otherwise Classified (HNOC)

May be harmful in contact with skin

Signal Word Danger

Hazard Statements

May cause cancer



Precautionary Statements - Prevention

Obtain special instructions before use

Do not handle until all safety precautions have been read and understood

Use personal protective equipment as required

Precautionary Statements - Response

If exposed or concerned: Get medical advice/attention

Precautionary Statements - Storage

Store locked up

Store in a well-ventilated place. Keep container tightly closed

Precautionary Statements - Disposal

Dispose of contents/container to an approved waste disposal plant

Unknown Acute Toxicity

90% of the mixture consists of ingredient(s) of unknown toxicity

3. COMPOSITION/INFORMATION ON INGREDIENTS

Chemical Name	CAS No	Weight-%
Proprietary mineral	Proprietary	56-58
Proprietary mineral	Proprietary	21-23
Proprietary solvent	Proprietary	5-10
Proprietary plasticizer	Proprietary	1-10
Proprietary mineral	Proprietary	1-10
Proprietary surfactant	Proprietary	1-10
Cellulose Fiber	9004-34-6	1-10
Carbon Black	1333-86-4	1-10
Titanium Dioxide	13463-67-7	1-10

^{**}If Chemical Name/CAS No is "proprietary" and/or Weight-% is listed as a range, the specific chemical identity and/or percentage of composition has been withheld as a trade secret.**

4. FIRST-AID MEASURES

First Aid Measures

General Advice IF exposed: Call a POISON CENTER or doctor/physician.

Eye Contact Immediately flush with plenty of water. After initial flushing, remove any contact lenses and

continue flushing for at least 15 minutes. Get medical attention if irritation occurs.

Skin Contact Wash with soap and water. Get medical attention if irritation occurs.

Inhalation Remove to fresh air.

Ingestion If large quantities are swallowed, get emergency medical help immediately.

Most important symptoms and effects

Symptoms May cause skin and eye irritation. Ingestion of large quantities (more than a few ounces)

may cause upset stomach, diarrhea, nausea, and vomiting.

Indication of any immediate medical attention and special treatment needed

Notes to Physician Treat symptomatically.

5. FIRE-FIGHTING MEASURES

Suitable Extinguishing Media

Dry chemical. Carbon dioxide (CO2). Foam.

Unsuitable Extinguishing Media Not determined.

Specific Hazards Arising from the Chemical

Possible products of thermal degradation include carbon monoxide and carbon dioxide. Thermal decomposition can lead to release of irritating and toxic gases and vapors.

Hazardous Combustion Products Carbon monoxide. Carbon dioxide (CO2). Hydrocarbons.

Protective equipment and precautions for firefighters

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

6. ACCIDENTAL RELEASE MEASURES

Personal precautions, protective equipment and emergency procedures

Personal PrecautionsUse personal protective equipment as required.

Environmental Precautions See Section 12 for additional Ecological Information.

Methods and material for containment and cleaning up

Methods for Containment Prevent further leakage or spillage if safe to do so.

Methods for Clean-Up Absorb spillage with non-combustible, absorbent material. Place in appropriate containers

for disposal.

7. HANDLING AND STORAGE

Precautions for safe handling

Advice on Safe Handling Obtain special instructions before use. Do not handle until all safety precautions have been

read and understood. Use personal protective equipment as required. Handle in

accordance with good industrial hygiene and safety practice.

Conditions for safe storage, including any incompatibilities

Storage Conditions Keep container tightly closed and store in a cool, dry and well-ventilated place. Store in a

cool place (49°C, 120°F).

Incompatible Materials Strong solvents.

8. EXPOSURE CONTROLS/PERSONAL PROTECTION

Exposure Guidelines

Chemical Name	ACGIH TLV	OSHA PEL	NIOSH IDLH
Proprietary mineral	-	TWA: 15 mg/m ³ total dust TWA: 5 mg/m ³ respirable fraction	TWA: 10 mg/m³ total dust TWA: 5 mg/m³ respirable dust
		(vacated) TWA: 15 mg/m ³ total	
		dust	
		(vacated) TWA: 5 mg/m ³	
		respirable fraction	
Proprietary mineral	TWA: 2 mg/m³ particulate matter	TWA: 15 mg/m³ total dust	TWA: 10 mg/m³ total dust
	containing no asbestos and <1%	TWA: 5 mg/m ³ respirable fraction	TWA: 5 mg/m ³ respirable dust
	crystalline silica, respirable fraction	(vacated) TWA: 10 mg/m ³ total	
	Haction	dust	
		(vacated) TWA: 5 mg/m ³	
		respirable fraction	
Proprietary mineral	TWA: 2 mg/m ³ particulate matter	(vacated) TWA: 2 mg/m ³	IDLH: 1000 mg/m ³
	containing no asbestos and <1%	respirable dust <1% Crystalline	TWA: 2 mg/m³ containing no
	crystalline silica, respirable	silica, containing no Asbestos	Asbestos and <1% Quartz
	fraction	TWA: 20 mppcf if 1% Quartz or	respirable dust
Cellulose Fiber	TWA: 10 mg/m ³	more, use Quartz limit TWA: 15 mg/m³ total dust	TWA: 10 mg/m ³ total dust
9004-34-6	TWA. 10 Hig/III	TWA: 15 mg/m³ respirable	TWA: 10 mg/m total dust TWA: 5 mg/m ³ respirable dust
3004 04 0		fraction	1 vvv. o mg/m Teophable dust
		(vacated) TWA: 15 mg/m³ total	
		dust	
		(vacated) TWA: 5 mg/m ³	
		respirable fraction	
Carbon Black	TWA: 3 mg/m³ inhalable fraction	TWA: 3.5 mg/m ³	IDLH: 1750 mg/m ³
1333-86-4		(vacated) TWA: 3.5 mg/m ³	TWA: 3.5 mg/m ³ TWA: 0.1 mg/m ³ Carbon black in
			presence of Polycyclic aromatic
			hydrocarbons PAH
Titanium Dioxide	TWA: 10 mg/m ³	TWA: 15 mg/m³ total dust	IDLH: 5000 mg/m ³
13463-67-7		(vacated) TWA: 10 mg/m ³ total	
		dust	

Other Information If product is sanded, appropriate respirator should be worn to avoid breathing dust.

Pre-existing respiratory disorders may be aggravated by exposure. If sanded, this material may generate silica / titanium dust. Inhaled silica / titanium has been classified by IARC as

a human carcinogen (see section 11).

Appropriate engineering controls

Engineering Controls Apply technical measures to comply with the occupational exposure limits.

Individual protection measures, such as personal protective equipment

Eye/Face Protection Use approved eye protection to avoid eye contact.

wear gloves for routine industrial use.

Respiratory Protection Ensure adequate ventilation, especially in confined areas.

General Hygiene Considerations Handle in accordance with good industrial hygiene and safety practice.

9. PHYSICAL AND CHEMICAL PROPERTIES

Information on basic physical and chemical properties

Physical State Semi-solid

Appearance Dark gray-green soft solid Odor Slight characteristic odor

COC

Color Dark gray-green Odor Threshold Not determined

<u>Property</u> <u>Values</u> <u>Remarks • Method</u>

PH Not determined
Melting Point/Freezing Point Not determined
Boiling Point/Boiling Range Not determined
Flood Point

Flash Point 232 °C / 450 °F

Evaporation Rate
Flammability (Solid, Gas)
Upper Flammability Limits
Lower Flammability Limit
Vapor Pressure
Vapor Density
Not determined
Not determined
Not determined
Not determined

Specific Gravity 1.800

Water Solubility Not determined Solubility in other solvents Not determined **Partition Coefficient** Not determined **Auto-ignition Temperature** Not determined **Decomposition Temperature** Not determined **Kinematic Viscosity** Not determined **Dynamic Viscosity** Not determined **Explosive Properties** Not determined **Oxidizing Properties** Not determined

10. STABILITY AND REACTIVITY

Reactivity

Not reactive under normal conditions.

Chemical Stability

Stable under recommended storage conditions.

Possibility of Hazardous Reactions

None under normal processing.

Hazardous Polymerization Under normal conditions of storage and use, hazardous polymerization will not occur.

Conditions to Avoid

Keep out of reach of children.

Incompatible Materials

Strong solvents.

Hazardous Decomposition Products

Hydrocarbons. Smoke, fumes or vapors, and oxides of carbon.

11. TOXICOLOGICAL INFORMATION

Information on likely routes of exposure

Product Information

Eye Contact May be irritating to the eye.

Skin Contact May be harmful in contact with skin.

Inhalation Do not inhale.

Ingestion Swallowing large amounts may cause digestive discomfort.

Component Information

Chemical Name	Oral LD50	Dermal LD50	Inhalation LC50	
Proprietary solvent	> 5000 mg/kg (Rat)	> 2000 mg/kg (Rabbit)	= 2.18 mg/L (Rat) 4 h	
Cellulose Fiber 9004-34-6	> 5 g/kg (Rat)	> 2 g/kg (Rabbit)	> 5800 mg/m³ (Rat) 4 h	
Carbon Black 1333-86-4	> 15400 mg/kg (Rat)	> 3 g/kg (Rabbit)	-	
Titanium Dioxide 13463-67-7	> 10000 mg/kg (Rat)	-	-	

Information on physical, chemical and toxicological effects

Symptoms Please see section 4 of this SDS for symptoms.

Delayed and immediate effects as well as chronic effects from short and long-term exposure

Carcinogenicity Group 2B IARC components are "possibly carcinogenic to humans". Titanium dioxide is a

possible carcinogen when it appears as a respirable dust. Wood dust particles are considered to be a human carcinogen when in respirable form (dust / powder). Carbon

black is a possible carcinogen when it appears as a respirable dust.

Chemical Name	ACGIH	IARC	NTP	OSHA
Proprietary solvent	A2	Group 1		Х
Proprietary mineral		Group 3		
Cellulose Fiber 9004-34-6		Group 1		
Carbon Black 1333-86-4	A3	Group 2B		Х
Titanium Dioxide 13463-67-7		Group 2B		Х

Legend

ACGIH (American Conference of Governmental Industrial Hygienists)

A3 - Animal Carcinogen

IARC (International Agency for Research on Cancer)

Group 1 - Carcinogenic to Humans

Group 2B - Possibly Carcinogenic to Humans

Group 3 IARC components are "not classifiable as human carcinogens"

OSHA (Occupational Safety and Health Administration of the US Department of Labor)

X - Present

Numerical measures of toxicity

Not determined

Unknown Acute Toxicity 90% of the mixture consists of ingredient(s) of unknown toxicity.

12. ECOLOGICAL INFORMATION

Ecotoxicity

The product is not classified as environmentally hazardous. However, this does not exclude the possibility that large or frequent spills can have a harmful or damaging effect on the environment.

Component Information

Chemical Name	Algae/aquatic plants	Fish	Toxicity to microorganisms	Crustacea
Proprietary solvent		5000: 96 h Oncorhynchus		1000: 48 h Daphnia magna
		mykiss mg/L LC50		mg/L EC50
Proprietary mineral		100: 96 h Brachydanio rerio		
		g/L LC50 semi-static		
Carbon Black				5600: 24 h Daphnia magna
1333-86-4				mg/L EC50

Persistence/Degradability

Not determined.

Bioaccumulation

Not determined.

Mobility

Not determined

Other Adverse Effects

Not determined

13. DISPOSAL CONSIDERATIONS

Waste Treatment Methods

Disposal of Wastes Disposal should be in accordance with applicable regional, national and local laws and

regulations.

Contaminated Packaging Disposal should be in accordance with applicable regional, national and local laws and

regulations.

14. TRANSPORT INFORMATION

Note Please see current shipping paper for most up to date shipping information, including

exemptions and special circumstances.

DOT Not regulated

IATA Not regulated

IMDG Not regulated

15. REGULATORY INFORMATION

International Inventories

All ingredients are listed in the Australian Inventory of Chemical Substances (AICS)

Legend:

TSCA - United States Toxic Substances Control Act Section 8(b) Inventory

DSL/NDSL - Canadian Domestic Substances List/Non-Domestic Substances List

EINECS/ELINCS - European Inventory of Existing Chemical Substances/European List of Notified Chemical Substances

ENCS - Japan Existing and New Chemical Substances

IECSC - China Inventory of Existing Chemical Substances

KECL - Korean Existing and Evaluated Chemical Substances

PICCS - Philippines Inventory of Chemicals and Chemical Substances

AICS - Australian Inventory of Chemical Substances

US Federal Regulations

SARA 313

Not determined

US State Regulations

California Proposition 65

This product contains the following Proposition 65 chemicals.

Chemical Name		California Proposition 65
	Carbon Black - 1333-86-4	Carcinogen
	Titanium Dioxide - 13463-67-7	Carcinogen

U.S. State Right-to-Know Regulations

Chemical Name	New Jersey	Massachusetts	Pennsylvania
Proprietary mineral	X	X	X
Proprietary mineral	Х	Х	X
Proprietary mineral	Х	Х	Х
Cellulose Fiber 9004-34-6	Х	X	X
Carbon Black 1333-86-4	Х	Х	Х
Titanium Dioxide 13463-67-7	Х	Х	Х

16. OTHER INFORMATION

NFPA_	Health Hazards	Flammability	Instability	Special Hazards
	0	1	0	Not determined
<u>HMIS</u>	Health Hazards	Flammability	Physical Hazards	Personal Protection
	Not determined	Not determined	Not determined	Not determined

Issue Date:28-Apr-2014Revision Date:16-Dec-2019Revision Note:Periodic Review

Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text.

End of Safety Data Sheet