



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.


PANDUIT P/N	WEIGHT
SEE SHEET 2	SEE SHEET 2




**REAR VIEW**



**LEFT VIEW**



**FRONT VIEW**



**SIDE VIEW**

**SPECIFICATION:**

- STANDARD
  - UNIT TYPE: MONITORED INPUT
  - ORIENTATION: HORIZONTAL (1U)
  - OUTLET QTY & TYPE: (8)C13
  - INPUT VOLTAGE: 100-240VAC
  - INPUT FREQUENCY: 50/60HZ
  - INPUT CURRENT: 16A
  - BREAKER QTY & TYPE: NONE
  - INPUT PHASE: SINGLE-PHASE
  - RATED POWER: 3.7 kVA
  - INPUT PLUG: IEC C20 100-240V LNLET
  - INPUT POWER CORD: SEE SHEET 2 PART NUMBER TABLE
  - REGULATORY STANDARD: RoHS COMPLIANT
- ADDITIONAL: NONE
- ACCESSORIES:
  - DOCUMENTATION KIT
  - PRODUCT SAFETY WARNING SHEET
  - QTY: (4) M6 X 12 PAN HEAD MACHINE SCREW
  - QTY: (4) M6 CAGE NUT

**NOTES:**

- PRIMARY DIMENSIONS ARE IN MILLIMETERS. SECONDARY DIMENSIONS ARE IN [INCHES]
- INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE, AND LOCAL CODES
- VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART
- FOR FULL PRODUCT FUNCTIONALITY REFER TO USER MANUAL
- DRAWING VIEWS SHOW THE INPUT CORD IN THE "TOP END FED" CONFIGURATION

**IDENTIFICATION:**

FOR FINISHED GOOD PART NUMBER & DESCRIPTION TABLE SEE SHEET 2 CONFIGURABLE PART NUMBERS: E08D01M-XXYZ

XX: FINISHED GOOD COLOR BL=BLACK YL=YELLOW BU=BLUE RD=RED WH=WHITE GN=GREEN	Y: INPUT FEED TYPE 1=TOP-END FED 2=BOTTOM-END FED	Z: INPUT CORD LENGTH A=1 METER B=2 METER C=3 METER
--	---	---

**PLUG / RECEPTACLE BLOCK**



**PLUG**  
IEC 60320/C20  
16A, 250V MAX RATED INPUT



**RECEPTACLE**  
IEC 60320 C13  
10A, 250V MAX RATED OUTPUT

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
00A	08/29/2023	LL	MIM	MJD	INITIAL RELEASE	E08D01M

WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGN THE CLIENT SIGNATURE BOX. THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY.		SIGN
		DATE
		PRINT
TITLE <b>INTELLIGENT SERIES PDU E08D01M</b> CONTROL DRAWING		
ITEM REVISION NAME:		<b>PANDUIT</b>
DATASHEET FILE NAME:		
UNLESS OTHERWISE SPECIFIED DIMENSIONAL TOLERANCE ARE: mm [IN] Tolerance (mm) 0<L≤50 ±0.5 50<L≤250 ±1.0 250<L≤500 ±1.5 500<L≤1000 ±2.5 1000<L≤2000 ±4.0		MATERIAL/COLOR: <b>N/A</b>
THIRD ANGLE PROJECTION		DRAWING NUMBER: <b>E08D01M_DC</b>
DRAWN BY	DATE	SCALE
LL	08/29/2023	NONE
CHK	MIM	SCALE
SHT 1 OF 2		<b>B</b>

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

FINISHED GOOD PART NUMBER	FINISHED GOOD DESCRIPTION	COLOR	INPUT CORD LENGTH	WEIGHT
E08D01M	MI PDU, 16A, (8)C13, IEC C20 INLET, BLACK	BLACK (RAL 9005)	IEC C19 TO C20 3M(+254MM/-127MM)[10'(+10"/-5")]	1.7kg

00A	08/29/2023	LL	MIM	MJD	INITIAL RELEASE	E08D01M
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN

WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGN THE CLIENT SIGNATURE BOX. THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY.		SIGN
		DATE
		PRINT
TITLE <b>INTELLIGENT SERIES PDU E08D01M</b> CONTROL DRAWING		
ITEM REVISION NAME:		<b>PANDUIT</b>
DATASHEET FILE NAME:		
UNLESS OTHERWISE SPECIFIED DIMENSIONAL TOLERANCE ARE: mm [IN]		MATERIAL/COLOR: N/A
Tolerance (mm) 0 < L ≤ 50 ±0.5 50 < L ≤ 250 ±1.0 250 < L ≤ 500 ±1.5 500 < L ≤ 1000 ±2.5 1000 < L ≤ 2000 ±4.0		DRAWING NUMBER: E08D01M_DC
THIRD ANGLE PROJECTION	SCALE NONE	SHT 2 OF 2
DRAWN BY LL	DATE 08/29/2023	SCALE B