


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	WEIGHT
P42E24M-XXYZ	SEE SHEET 2




UNIT TYPE: MONITORED SWITCHED
 ORIENTATION: VERTICAL, 0U FULL
 OUTLET QTY&TYPE: (21)C13/C15,(21)C13/C15/C19
 INPUT VOLTAGE: 200-240VAC
 INPUT CURRENT: 60A (48A DERATED)
 BREAKER QTY&TYPE: (6) 20AMP, DOUBLE-POLE
 INPUT PHASE: THREE-PHASE DELTA
 RATED POWER: 17.3 KVA
 INPUT PLUG: IEC 60309,3P 4W,9H,60A(48A DERATED) (IP44)
 INPUT POWER CORD: SEE SHEET 2 PART NUMBER TABLE
 REGULATORY STANDARD: RoHS COMPLIANT

2. ADDITIONAL: NONE
 3. ACCESSORIES: (1) PRODUCT SAFETY WARNING SHEET


NOTES:
 1. PRIMARY DIMENSIONS ARE IN MILLIMETERS. SECONDARY DIMENSION ARE IN [INCHES]
 2. INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE, AND LOCAL CODES
 3. VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART
 4. FOR FULL PRODUCT FUNCTIONALITY REFER TO USER MANUAL
 5. DRAWING VIEWS SHOW THE INPUT CORD IN THE "TOP END FED" CONFIGURATION

B

B




INPUT CORD LENGTH SEE IDENTIFICATION TABLE




IDENTIFICATION

FOR FINISHED GOOD PART NUMBER & DESCRIPTION TABLE SEE SHEET 2 CONFIGURABLE PART NUMBERS: P42E24M-XX Y Z



BOTTOM VIEW



FRONT VIEW

PLUG/RECEPTACLE BLOCK



PLUG
 IEC 60309, 3P 4W,9H
 IP44 (SPASHPROOF)
 60A,250V,3-PHASE MAX
 RATED INPUT 48A DERATED



RECEPTACLES
 C13/C15 COMBO
 10A, 250V MAX RATED OUTPUT



RECEPTACLES
 C13/C15/C19 COMBO
 16A, 250V MAX RATED OUTPUT

A

A

WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGN THE CLIENT SIGNATURE BOX. THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY.		SIGN
		DATE
		PRINT
TITLE INTELLIGENT SERIES PDU P42E24M-XXYZ CUSTOMER DRAWING		
ITEM REVISION NAME:		
DATASHEET FILE NAME:		
UNLESS OTHERWISE SPECIFIED DIMENSIONAL TOLERANCE ARE: mm [IN]		MATERIAL/COLOR:
Tolerance(mm) 0-1<50 ±0.5 50-1<250 ±1.0 250-1<500 ±1.5 500-1<1000 ±2.5 1000-1<2000 ±4.0		N/A
THIRD ANGLE PROJECTION		DRAWING NUMBER: P42E24M-XXYZ_DC
DRAWN BY: LRF	DATE: 06/16/2023	CHK: LJB
SCALE: NONE	SHT 1 OF 2	
ECN	SCALE: B	

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
02A	06/16/2023	LRF	CSH	MJD	Update outlet layout	P42E24M-XXYZ
01A	04/25/2023	LRF	CSH	MJD	INITIAL RELEASE	P42E24M-XXYZ

2

1

2



1

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

FINISHED GOOD PART NUMBER	FINISHED GOOD DESCRIPTION	COLOR	INPUT CORD LENGTH	WEIGHT
P42E24M	VERTICAL,(21) C13/C15,(21)C13/15/C19,MONITORED SWITCHED,200-240VAC/60A(48A DERATED) / 3PHASE, TOP-END FED, 3 METER INPUT CORD, BLACK	BLACK (RAL 9005)	3M(+254mm/-127mm) 10' [+10"/-5"]	13.2kg

B

B

A

A

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
02A	06/16/2023	LRF	CSH	MJD	Update outlet layout	P42E24M-XYZ
01A	04/25/2023	LRF	CSH	MJD	INITIAL RELEASE	P42E24M-XYZ

WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGN THE CLIENT SIGNATURE BOX. THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY		SIGN
		DATE
		PRINT
TITLE INTELLIGENT SERIES PDU P42E24M-XYZ CUSTOMER DRAWING		
ITEM REVISION NAME:		PANDUIT
DATASHEET FILE NAME:		
UNLESS OTHERWISE SPECIFIED DIMENSIONAL TOLERANCE ARE: mm [IN]		MATERIAL/COLOR: N/A
THIRD ANGLE PROJECTION Tolerance(mm) 0<L<50 ±0.5 50<L<250 ±1.0 250<L<500 ±1.5 500<L<1000 ±2.5 1000<L<2000 ±4.0		DRAWING NUMBER: P42E24M-XYZ_DC
DRAWN BY	DATE	SCALE
LRF	06/16/2023	NONE
CHK	LJB	SCALE
SHT 2 OF 2		B

2



1