

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	WEIGHT
SEE SHEET 2	SEE SHEET 2

SPECIFICATION:


- STANDARD
 UNIT TYPE: MONITORED PER OUTLET
 ORIENTATION: VERTICAL, 0U FULL
 OUTLET QTY & TYPE: (20)C13, (4)C19
 INPUT VOLTAGE: 100-240VAC
 INPUT FREQUENCY: 50/60HZ
 INPUT CURRENT: 16A
 BREAKER QTY & TYPE: NONE
 INPUT PHASE: SINGLE-PHASE
 RATED POWER: 3.7 kVA
 INPUT PLUG: IEC 60309 2P+E 6H 16A
 INPUT POWER CORD: SEE SHEET 2 PART NUMBER TABLE
 REGULATORY STANDARD: RoHS COMPLIANT
- ADDITIONAL:
NONE
- ACCESSORIES:
DOCUMENTATION KIT
PRODUCT SAFETY WARNING SHEET

NOTES:

- PRIMARY DIMENSIONS ARE IN MILLIMETERS. SECONDARY DIMENSIONS ARE IN [INCHES]
- INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE, AND LOCAL CODES
- VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART
- FOR FULL PRODUCT FUNCTIONALITY REFER TO USER MANUAL
- DRAWING VIEWS SHOW THE INPUT CORD IN THE "TOP END FED" CONFIGURATION

IDENTIFICATION:

FOR FINISHED GOOD PART NUMBER & DESCRIPTION TABLE SEE SHEET 2 CONFIGURABLE PART NUMBERS: E24F09M-XXYZ




WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGN THE CLIENT SIGNATURE BOX. THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY.	SIGN
	DATE
	PRINT

TITLE	INTELLIGENT SERIES PDU E24F09M CONTROL DRAWING
ITEM REVISION NAME:	
DATASHEET FILE NAME:	


UNLESS OTHERWISE SPECIFIED DIMENSIONAL TOLERANCE ARE: mm [IN]	MATERIAL/COLOR: N/A
--	------------------------

THIRD ANGLE PROJECTION	DRAWING NUMBER: E24F09M_DC
DRAWN BY: LL DATE: 08/29/2023 CHK: MIM SCALE: NONE	SHT 1 OF 2 SCALE: B


LEFT VIEW



REAR VIEW




RIGHT VIEW



FRONT VIEW

BOTTOM VIEW




PLUG / RECEPTACLE BLOCK



PLUG
IEC 60309 2P+E 6H
IP44 (SPASHPROOF)
16A, 250VAC MAX RATED INPUT



RECEPTACLE
IEC 60320 C13
10A, 250V MAX RATED OUTPUT




RECEPTACLE
IEC 60320 C19
16A, 250V MAX RATED OUTPUT

00A	08/29/2023	LL	MIM	MJD	INITIAL RELEASE	E24F09M
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

FINISHED GOOD PART NUMBER	FINISHED GOOD DESCRIPTION	COLOR	INPUT CORD LENGTH	WEIGHT
E24F09M	MPO PDU, 16A, (20)C13 (4)C19, IEC 60309 2P+E 6h IP44-3M, TOP-FED, BLACK	BLACK(RAL 9005)	3M(+254MM/-127MM)[10'(+10"/-5")]	6.2kg

00A	08/29/2023	LL	MIM	MJD	INITIAL RELEASE	E24F09M
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN

WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGN THE CLIENT SIGNATURE BOX. THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY.				SIGN																		
				DATE																		
				PRINT																		
TITLE INTELLIGENT SERIES PDU E24F09M CONTROL DRAWING																						
ITEM REVISION NAME:				PANDUIT																		
DATASHEET FILE NAME:																						
UNLESS OTHERWISE SPECIFIED DIMENSIONAL TOLERANCE ARE: mm [IN]				MATERIAL/COLOR:																		
<table border="0"> <tr> <td></td> <td>Tolerance (mm)</td> <td></td> </tr> <tr> <td>0 < L ≤ 50</td> <td>±0.5</td> <td></td> </tr> <tr> <td>50 < L ≤ 250</td> <td>±1.0</td> <td></td> </tr> <tr> <td>250 < L ≤ 500</td> <td>±1.5</td> <td></td> </tr> <tr> <td>500 < L ≤ 1000</td> <td>±2.5</td> <td></td> </tr> <tr> <td>1000 < L ≤ 2000</td> <td>±4.0</td> <td></td> </tr> </table>					Tolerance (mm)		0 < L ≤ 50	±0.5		50 < L ≤ 250	±1.0		250 < L ≤ 500	±1.5		500 < L ≤ 1000	±2.5		1000 < L ≤ 2000	±4.0		N/A
	Tolerance (mm)																					
0 < L ≤ 50	±0.5																					
50 < L ≤ 250	±1.0																					
250 < L ≤ 500	±1.5																					
500 < L ≤ 1000	±2.5																					
1000 < L ≤ 2000	±4.0																					
 THIRD ANGLE PROJECTION				DRAWING NUMBER:																		
				E24F09M_DC																		
DRAWN BY	DATE	CHK	SCALE																			
LL	08/29/2023	MIM	NONE	SHT 2 OF 2																		
				SCALE B																		