

G6 Intelligent Power Distribution Unit (iPDU)

USGv6 Certified

PANDUIT[®]
SPECIFICATION SHEET

OVERVIEW

The best just got better. The G6 iPDU is more than a power distribution unit and energy monitoring device. These iPDU's monitor the data center power and environment (at the rack or cabinet level), by continuously scanning for electrical circuit overloads, and physical environmental conditions that place critical IT equipment at risk. The iPDU's provide comprehensive, accurate, energy measurement data to efficiently use power resources, make informed capacity planning decisions, improve uptime, measure PUE (power usage effectiveness), and drive green data center initiatives to save energy and money.

Making the right choice in IT equipment is essential for a safe, efficient data center operation. Panduit's full range of G6 iPDU's, environmental sensors, and dual locking power cords are the key to fulfilling mission-critical data center needs.

TECHNICAL INFORMATION

Dimensions:	Width In. (mm)	Depth In. (mm)	Height In. (mm)
0U HALF:	2 (52)	2.1 (53)	36.1 (917)
0U MID:	2 (52)	2.1 (53)	58.6 (1490)
0U FULL:	2 (52)	2.1 (53)	69 (1750)
0U FULL Wide:	3.3 (85)	2.1 (53)	69 (1750)

Mounting: Vertical units provide up to 48 outlets without encroaching on the EIA space.

KEY FEATURES AND BENEFITS

Combination outlets¹:	Combination outlets provide the ultimate in flexibility by allowing a customer to use an outlet as either an C13/C15 outlet or a C13/C15/C19/C21 outlet respectively. All combination outlets also accept the Panduit dual locking power cords to eliminate accidental disconnects.
Dual rated PDUs:	Simplify your supply chain by selecting a Dual Rated PDU. Dual rated PDUs have ratings and NRTL approvals for both North American & EMEA on the same part number.
HotSwappable controller:	Replace the controller and display module without having to power down the rack
Redundant network access:	Specifically designed for Landlord/Tenant (Co-Lo's) allowing for remote access of real-time, vital statistics and operating information on two separate, secure networks
Hardened security:	NMP v3, TLS, Encrypted Security; allows for Panduit PDUs to pass standard popular industry certified security scans. USGv6 Certified IPv6 Stack
Dual 1GB Ethernet:	Reduces deployment time by auto-negotiating with data center level network switches and can daisy chain up to 32 iPDU's on a single IP address using only one network switch port
Plug & play sensors:	Digital sensors not only allow for multiple sensors on the same bus; but also identify themselves to the controller to simplify setup and commissioning
Multi-color PDUs:	Different color PDU's simplify power feed identification in redundant power schemes
Mobile & desktop friendly web GUI:	Enhanced web interface that detects the type of device that you are on (laptop, tablet or smart phone); and automatically adjusts the screen for an optimal experience
Mobile and desktop friendly web GUI:	Enhanced web interface that detects the type of device the user is on (laptop, tablet, or smart phone), and automatically adjusts the screen for an optimal experience
Outlet density:	Meets demands of densely packed IT equipment in rack or cabinet space
Form factor:	Optimal form factor enables efficient rack space utilization and airflow
Operating temperature:	60°C ambient at full load for operational reliability in high temperature areas
Cable retention:	Innovative cable tie accepting outlets allow for secure cord retention (C13 & C19 only) using a cable tie for added safety and security. (Panduit part number: PLT21-C0)
Circuit breakers:	Protects data center equipment for increased reliability by interrupting potentially hazardous circuit over-current conditions*
Color coded circuits²	Easily identify phase to outlet banks to aid in fault isolation or load balancing
External chassis ground:	Meets NEC requirements and installation guidelines for IT equipment
Load balancing:	Monitored through visual display on oLED (for three-phase units only)
Multiple input plug options:	A full breadth offering to seamlessly interoperate with existing building power wiring schemes
Multiple mounting options:	Enables simple out of the box commissioning and flexibility with Panduit cabinets and industry standard mounting features enabling installation into third party cabinets
Mounting buttons:	Allows tool-less mounting of rack PDUs for faster installations on vertical 0U units
Supported metering:	Frequency, VA, PF, plus aggregate and per phase Amperage, Voltage, Wattage, and Kilowatts per hour

¹ Applies to products outfitted with combination outlets

² Applies to products outfitted with circuit breakers



G6 Intelligent Power Distribution Unit (iPDU) USGv6 Certified

iPDU PRODUCT FAMILIES

MI series:	Rack PDUs that have the ability for aggregate power monitoring to quickly identify potential power issues, and reclaim available or under-utilized power capacity.
MS series:	Rack PDUs that have the ability for aggregate power monitoring and outlet level switching capabilities for individual outlets or a group of outlets. Enabling power sequencing, rebooting equipment or restrict unauthorized use of individual outlets.
MPO series:	Rack PDUs that have the ability for outlet level (and aggregate) power monitoring to quickly identify potential power issues, and reclaim available or under-utilized power capacity at the outlet level enabling the redeployment or decommissioning of individual servers to reclaim available or under-utilized power capacity.
MSPO series:	Rack PDUs that have the ability for outlet level (and aggregate) power monitoring and outlet level switching capabilities for individual outlets or a group of outlets. Power monitoring at the individual outlet level provides actionable management data on the power consumption of each connected IT device enabling the redeployment or decommissioning of individual servers to reclaim available or under-utilized power capacity. Ideal for remote power reset, and cabinet power on sequencing and restrict unauthorized use of individual outlets.

ELECTRICAL SPECIFICATIONS

Input voltage:	North America <ul style="list-style-type: none">• Single-Phase 120 V• Single-Phase 208 V• Three-Phase Delta 208 V• Three-Phase Wye 120/208 V• Three-Phase Wye 415 V• Three-phase WYE 240/415 V	International models <ul style="list-style-type: none">• Single-Phase 240 V• Three-Phase Wye 240/415 V (for Japan 415 V only)• Three-Phase Delta 208 V
Input current (per phase):	North America <ul style="list-style-type: none">• 15A, 20A, 30A, 50A, 60A	International models <ul style="list-style-type: none">• 16A, 32A, 63A
Input power:	North America <ul style="list-style-type: none">• 1.4 - 34.5 (kVA)	International models <ul style="list-style-type: none">• 3.7 - 44.4 (kVA)
Input frequency:	50/60 Hz	
Output voltage:	120 - 240 VAC	
Maximum output current: (outlet)	IEC C13: 10A IEC C19: 16A NEMA 5-20R: 16A	
Overload protection (where applicable):	Circuit Breakers, hydraulic magnetic	
10 kAIC Circuit Breakers for all 415 V models for North America		

GENERAL SPECIFICATIONS

Temperature (operating):	50°F to 140°F (10°C to 60°C)		
Temperature (storage):	-4°F to 140°F (-20°C to 60°C)		
Relative humidity (operating):	10% to 90% non-condensing		
Relative humidity (non-operating):	5% to 95% RH		
Relative humidity (storage):	5% to 95%		
Elevation (operating):	0 to 10,000 ft. (0 to 3000m)		
Elevation (storage):	0 to 30,000 ft. (0 to 9144m)		
Conformance (standards):	USA & Canada ³ - UL, CB Test Approved File number: E218078 Mexico: NOM Approved ³ Europe - CE/UKCA Approved³ Australia - RCM Approved ³ Brazil: Approved	Chile: Approved Peru: Approved Uruguay: Approved Costa Rica: Approved United Arab Emirates (UAE): Approved	India: Approved China: Approved Hong Kong: Approved Singapore: Approved Indonesia: Approved Philippines: Approved
Environmental compliances:	RoHS & REACH		

³ Applies to select products

CABINET COMPATIBILITY

Intelligent PDUs can be easily installed into Panduit (or third-party cabinets) by utilizing the installed mounting buttons (18.4mm diameter). Where necessary, a small diameter (14.5mm) mounting button is available (sold separately, P/N: MA018). Panduit PDUs feature threaded inserts on the back and both sides for the ultimate in mounting flexibility. They safely and efficiently manage and distribute power to multiple devices through a single input power connector, per PDU, to enhance scalability of network build outs.

G6 Intelligent Power Distribution Unit (iPDU) USGv6 Certified

PRODUCT SPECIFICATIONS

MI SERIES

	Panduit Part Number	Region	Input Current per Phase	Form Factor	Input Plug Type	Circuit Breakers	Apparent Power (kVA)	Outlet Count	Outlet Configuration	Width inches (mm)	Depth inches (mm) at Outlet position"	Height inches (mm)
100-240VAC, 1 PHASE	P42D06G	EMEA	32	OU FULL	IEC 60309 2P+E 6h 32A (IP44)	2	7.4	42	(36)C13 (6)C19	2 (52)	2.1 (53)	69 (1750)
	P38D25G	NA	30	OU FULL	NEMA L6-30P	2	5	38	(32)C13 (6)C19	2 (52)	2.1 (53)	69 (1750)
	P24D03G	EMEA	32	OU MID	IEC 60309 2P+E 6h 32A (IP44)	2	7.4	24	(20)C13 (4)C19	2 (52)	2.1 (53)	69 (1750)
	P34D41G	EMEA	32	OU FULL	IEC 60309 2P+E 6h 32A (IP44)	2	7.4	34	(28)C13 (6)C19	2 (52)	2.1 (53)	69 (1750)
	P24D40G	EMEA	16	OU MID	IEC 60309 2P+E 6h 16A (IP44)	0	3.7	24	(20)C13 (4)C19	2 (52)	2.1 (53)	69 (1750)
	P24D24G	NA	20	OU MID	NEMA L6-20P	0	3.3	24	(20)C13 (4)C19	2 (52)	2.1 (53)	69 (1750)
	P24D07G	NA	30	OU MID	NEMA L6-30P	2	5	24	(20)C13 (4)C19	2 (52)	2.1 (53)	69 (1750)
	P24D23G	NA	30	OU MID	NEMA L5-30P	2	2.9	24	(24)5-20R	2 (52)	2.1 (53)	69 (1750)
	P36D26G	NA	50	OU FULL	CS8265	3	8.3	36	(30)C13 (6)C19	2 (52)	2.1 (53)	69 (1750)
	P16D20G	NA	15	OU HALF	NEMA 5-15P	0	1.4	16	(16)5-20R	2 (52)	2.1 (53)	69 (1750)
208 VAC, 3 PHASE	P38D28G	NA	30	OU FULL	NEMA L21-30P	3	8.6	38	(30)C13 (6)C19 (2)5-20R	2 (52)	2.1 (53)	69 (1750)
	P36D08G	NA	30	OU FULL	NEMA L15-30P	3	8.6	36	(30)C13 (6)C19	2 (52)	2.1 (53)	69 (1750)
	P24D34G	NA	60	OU FULL	IEC 60309 3P+E 9h 60A (IP44)	6	17.3	24	(12)C13 (12)C19	2 (52)	2.1 (53)	69 (1750)
	P36D29G	NA	50	OU FULL	CS8365	3	10	36	(30)C13 (6)C19	2 (52)	2.1 (53)	69 (1750)
	P30D02G	NA	30	OU FULL	NEMA L21-30P	3	8.6	30	(18)C13 (6)C19 (6)5-20R	2 (52)	2.1 (53)	69 (1750)
	P24D01G	NA	30	OU MID	NEMA L21-30P	3	8.6	24	(18)C13 (6)C19	2 (52)	2.1 (53)	69 (1750)
	P48D21G	NA	30	OU FULL	NEMA L21-30P	3	8.6	48	(24)C13/C15 (24)C13/15/C19/C21	2.2 (56)	3 (75)	70 (1780)
	P48D22G	NA	30	OU FULL	NEMA L15-30P	3	8.6	48	(24)C13/C15 (24)C13/15/C19/C21	2.2 (56)	3 (75)	70 (1780)
	P42D20G	NA	60	OU FULL	IEC 60309 3P+E 9h 60A (IP44)	6	17.3	42	(21)C13/C15 (21)C13/15/C19/C21	2.2 (56)	3 (75)	70 (1780)
	P42D22G	NA	50	OU FULL	CS8365	6	14.4	42	(21)C13/C15 (21)C13/15/C19/C21	2.2 (56)	3 (75)	70 (1780)
P36D30G	NA	50	OU FULL	CS8365	6	14.4	36	(24)C13 (12)C19	2.2 (55)	3.1 (80)	70 (1780)	
P36D31G	NA	60	OU FULL	IEC 60309 3P+E 9h 60A (IP44)	6	17.3	36	(24)C13 (12)C19 	2.2 (55)	3.1 (80)	70 (1780)	

G6 Intelligent Power Distribution Unit (iPDU) USGv6 Certified

PRODUCT SPECIFICATIONS (CONTINUED)

MI SERIES

	Panduit Part Number	Region	Input Current per Phase	Form Factor	Input Plug Type	Circuit Breakers	Apparent Power (kVA)	Outlet Count	Outlet Configuration	Width inches (mm)	Depth inches (mm) at Outlet position"	Height inches (mm)
230/415 VAC, 3 PHASE	P42D04G	EMEA	32	OU FULL	IEC 60309 3P+N+E 6h 32A (IP44)	6	22	42	(30)C13 (12)C19	2 (52)	2.1 (53)	69 (1750)
	P30D05G	EMEA	16	OU MID	IEC 60309 3P+N+E 6h 16A (IP44)	0	11	30	(24)C13 (6)C19	2 (52)	2.1 (53)	69 (1750)
	P24D43G	EMEA	32	OU FULL	IEC 60309 3P+N+E 6h 32A (IP44)	6	22	24	(12)C13 (12)C19	2.2 (55)	2.1 (53)	69 (1750)
	P42D07G	NA	30	OU FULL +	NEMA L22-30P	6	17.3	42	(36)C13 (6)C19	2 (51)	2.1 (53)	69 (1750)
	P48D20G	NA/ EMEA	30/ 32	OU FULL	IEC 60309 3P+N+E 6h 30A/32A (IP44)	6	17.3/ 22.0	48	(24)C13/C15 (24)C13/15/C19/C21	2.2 (55)	3.1 (80)	70 (1780)
	P48D23G	NA/ EMEA	20/ 16	OU MID	IEC 60309 3P+N+E 6h 20A/16A (IP44)	0	11.5/ 11.0	48	(24)C13/C15 (24)C13/15/C19/C21	2.2 (56)	3 (75)	70 (1780)
	P42D21G	NA/ EMEA	60/ 63	OU FULL	IEC 60309 3P+N+E 6h 60A/63A (IP44)	12	43.5/ 34.6	42	(21)C13/C15 (21)C13/15/C19/C21	2.2 (56)	3 (75)	70 (1780)

MS SERIES

	Panduit Part Number	Region	Input Current per Phase	Form Factor	Input Plug Type	Circuit Breakers	Apparent Power (kVA)	Outlet Count	Outlet Configuration	Width inches (mm)	Depth inches (mm) at Outlet position"	Height inches (mm)
100-240VAC, 1 PHASE	P32E06G	NA/ EMEA	30 /32	OU FULL	IEC 60309 2P+E 6h 32A (IP44)	2	5.8/ 7.4	32	(24)C13 (8)C19	2 (52)	2.1 (53)	69 (1750)
	P24E28G	NA	30	OU FULL	NEMA L6-30P	2	5	24	(20)C13 (4)C19	2 (52)	2.1 (53)	69 (1750)
	P24E04G	EMEA	16	OU Mid	IEC 60309 2P+E 6h 16A (IP44)	0	3.7	24	(20)C13 (4)C19	2 (52)	2.1 (53)	69 (1750)
	P18E23G	NA	30	OU MID	NEMA L5-30P	2	2.9	18	(18)5-20R	2 (52)	2.1 (53)	69 (1750)
	P12E22G	NA	20	OU HALF	NEMA L5-20P	0	1.9	12	(12)5-20R	2 (52)	2.1 (53)	69 (1750)
	P16E27G	EMEA	16	OU HALF	IEC 60309 2P+E 6h 16A (IP44)	0	3.7	16	(12)C13 (4)C19	2 (52)	2.1 (53)	69 (1750)
	P16E24G	NA	20	OU HALF	NEMA L6-20P	0	3.3	16	(12)C13 (4)C19	2 (52)	2.1 (53)	69 (1750)
	P44E07G	EMEA	32	OU FULL - Wide	IEC 60309 2P+E 6h 32A (IP44)	2	7.4	44	(38)C13 (6)C19	2 (52)	2.1 (53)	69 (1750)
	P12E21G	NA	20	OU HALF	NEMA 5-20P	0	1.9	12	(12)5-20R	2 (52)	2.1 (53)	69 (1750)
	P12E20G	NA	15	OU HALF	NEMA 5-15P	0	1.4	12	(12)5-20R	2 (52)	2.1 (53)	69 (1750)

PRODUCT SPECIFICATIONS (CONTINUED)

MS SERIES (CONTINUED)

	Panduit Part Number	Region	Input Current per Phase	Form Factor	Input Plug Type	Circuit Breakers	Apparent Power (kVA)	Outlet Count	Outlet Configuration	Width inches (mm)	Depth inches (mm) at Outlet position"	Height inches (mm)
208 VAC, 3 PHASE	P24E32G	NA	32	0U FULL	IEC 60309 3P+N+E 6h 32A (IP44)	6	22	24	(12)C13 (12)C19	2 (52)	2.1 (53)	69 (1750)
	P36E35G	NA	16	0U MID	IEC 60309 3P+N+E 6h 16A (IP44)	0	11	36	(30)C13 (6)C19	2 (52)	2.1 (53)	69 (1750)
	P36E12G	NA	16	0U FULL	IEC 60309 3P+N+E 6h 16A (IP44)	0	11	36	(30)C13 (6)C19	2 (52)	2.1 (53)	69 (1750)
	P36E34G	NA	32	0U FULL	IEC 60309 3P+N+E 6h 32A (IP44)	6	22	36	(30)C13 (6)C19	2 (52)	2.1 (53)	69 (1750)
	P24E29G	NA	30	0U FULL +	NEMA L22-30P	6	17.3	24	(18)C13 (6)C19	2 (52)	2.1 (53)	69 (1750)
	P24E30G	NA	30/ 32	0U FULL	IEC 60309 3P+N+E 6h 30A/32A (IP44)	6	17.3/ 22.0	24	(18)C13 (6)C19	2 (52)	2.1 (53)	69 (1750)
	P48E21G	NA	20/ 16	0U MID	IEC 60309 3P+N+E 6h 20A/16A (IP44)	0	11.5/ 11.0	48	(24)C13/C15 (24)C13/15/C19/C21	2.2 (56)	3 (75)	70 (1780)
	P48E22G	NA	60/ 63	0U FULL	IEC 60309 3P+N+E 6h 60A/63A (IP44)	12	43.5/ 34.6	48	(24)C13/C15 (24)C13/15/C19/C21	2.2 (56)	3 (75)	70 (1780)
	P42E24G	NA	60	0U FULL	IEC 60309 3P+E 9h 60A (IP44)	6	17.3	42	(21)C13/C15 (21)C13/15/C19/C21	2.2 (56)	3 (75)	70 (1780)
	P42E26G	NA	50	0U FULL	CS8365	6	14.4	42	(21)C13/C15 (21)C13/15/C19/C21	2.2 (56)	3 (75)	70 (1780)
230/415 VAC, 3 PHASE	P24E02G	EMEA	16	0U FULL	IEC 60309 3P+N+E 6h 16A (IP44)	0	11	24	(18)C13 (6)C19	2 (52)	2.1 (53)	69 (1750)
	P24E03G	EMEA	32	0U FULL	IEC 60309 3P+N+E 6h 32A (IP44)	6	22	24	(12)C13 (12)C19	2 (52)	2.1 (53)	69 (1750)
	P36E08G	EMEA	16	0U FULL	IEC 60309 3P+N+E 6h 16A (IP44)	0	11	36	(30)C13 (6)C19	2 (52)	2.1 (53)	69 (1750)
	P48E20G	NA/ EMEA	30/ 32	0U FULL	IEC 60309 3P+N+E 6h 30A/32A (IP44)	6	17.3/ 22.0	48	(24)C13/C15 (24)C13/15/C19/C21	2.2 (56)	3 (75)	70 (1780)
	P48E23G	NA/ EMEA	20/ 16	0U MID	IEC 60309 3P+N+E 6h 20A/16A (IP44)	0	11.5/ 11.0	48	(24)C13/C15 (24)C13/15/C19/C21	2.2 (56)	3 (75)	70 (1780)
	P48E25G	NA/ EMEA	60/ 63	0U FULL	IEC 60309 3P+N+E 6h 60A/63A (IP44)	12	43.5/ 34.6	48	(24)C13/C15 (24)C13/15/C19/C21	3.3 (85)	3 (75)	70 (1780)

PRODUCT SPECIFICATIONS (CONTINUED)

MPO SERIES

	Panduit Part Number	Region	Input Current per Phase	Form Factor	Input Plug Type	Circuit Breakers	Apparent Power (kVA)	Outlet Count	Outlet Configuration	Width inches (mm)	Depth inches (mm) at Outlet position"	Height inches (mm)
100-240VAC, 1 PHASE	P32F10G	EMEA	32	0U FULL	IEC 60309 2P+E 6h 32A (IP44)	2	7.4	32	(24)C13 (8)C19	2 (52)	2.1 (53)	69 (1750)
	P36F15G	NA	30	0U FULL	NEMA L6-30P	2	5	36	(30)C13 (6)C19	2 (52)	2.1 (53)	69 (1750)
	P24F01G	NA	30	0U FULL	NEMA L6-30P	2	5	24	(20)C13 (4)C19	2 (52)	2.1 (53)	69 (1750)
230/415 VAC, 3 PHASE	P36F13G	EMEA	32	0U FULL - Wide	IEC 60309 3P+N+E 6h 32A (IP44)	6	22	36	(24)C13 (12)C19	3.3 (85)	2.1 (53)	69 (1750)
	P36F12G	EMEA	16	0U FULL	IEC 60309 3P+N+E 6h 16A (IP44)	0	11	36	(30)C13 (6)C19	2 (52)	2.1 (53)	69 (1750)

MSPO SERIES

	Panduit Part Number	Region	Input Current per Phase	Form Factor	Input Plug Type	Circuit Breakers	Apparent Power (kVA)	Outlet Count	Outlet Configuration	Width inches (mm)	Depth inches (mm) at Outlet position"	Height inches (mm)
100-240VAC, 1 PHASE	P36G18G	NA	30	0U FULL	NEMA L6-30P	2	5	36	(30)C13 (6)C19	2 (52)	2.1 (53)	69 (1750)
	P24G01G	NA	30	0U FULL	NEMA L6-30P	2	5	24	(20)C13 (4)C19	2 (52)	2.1 (53)	69 (1750)
	P24G06G	EMEA	32	0U FULL	IEC 60309 2P+E 6h 32A (IP44)	2	7.4	24	(20)C13 (4)C19	2 (52)	2.1 (53)	69 (1750)
	P32G13G	EMEA	32	0U FULL	IEC 60309 2P+E 6h 32A (IP44)	2	7.4	32	(24)C13 (8)C19	2 (52)	2.1 (53)	69 (1750)
	P44G14G	EMEA	32	0U FULL - Wide	IEC 60309 2P+E 6h 32A (IP44)	2	7.4	44	(38)C13 (6)C19	3.3 (85)	2.1 (53)	69 (1750)

G6 Intelligent Power Distribution Unit (iPDU) USGv6 Certified

PRODUCT SPECIFICATIONS (CONTINUED)

MSPO SERIES (CONTINUED)

	Panduit Part Number	Region	Input Current per Phase	Form Factor	Input Plug Type	Circuit Breakers	Apparent Power (kVA)	Outlet Count	Outlet Configuration	Width inches (mm)	Depth inches (mm) at Outlet position ¹	Height inches (mm)
208 VAC, 3 PHASE	P36G20G	NA	50	0U FULL	CS8365	3	10	36	(30)C13 (6)C19	2 (52)	2.1 (53)	69 (1750)
	P24G03G	NA	30	0U FULL	NEMA L21-30P	3	8.6	24	(18)C13 (6)C19	2 (52)	2.1 (53)	69 (1750)
	P36G19G	NA	30	0U FULL	NEMA L21-30P	3	8.6	36	(30)C13 (6)C19	2 (52)	2.1 (53)	69 (1750)
	P24G05G	NA	60	0U FULL	IEC 60309 3P+E 9h 60A (IP44)	6	17.3	24	(12)C13 (12)C19	2 (52)	2.1 (53)	69 (1750)
	P24G02G	NA	30	0U FULL	NEMA L15-30P	3	8.6	24	(18)C13 (6)C19	2 (52)	2.1 (53)	69 (1750)
	P48G31G	NA	30	0U FULL	NEMA L21-30P	3	8.6	48	(24)C13/C15 (24)C13/15/C19/C21	2.2 (56)	3 (75)	70 (1780)
	P48G32G	NA	30	0U FULL	NEMA L15-30P	3	8.6	48	(24)C13/C15 (24)C13/15/C19/C21	2.2 (56)	3 (75)	70 (1780)
	P42G20G	NA	60	0U FULL	IEC 60309 3P+E 9h 60A (IP44)	6	17.3	42	(21)C13/C15 (21)C13/15/C19/C21	2.2 (56)	3 (75)	70 (1780)
	P42G22G	NA	50	0U FULL	CS8365	6	14.4	42	(21)C13/C15 (21)C13/15/C19/C21	2.2 (56)	3 (75)	70 (1780)
	P36G30G	NA	50	0U FULL	CS8365	6	14.4	36	(24)C13 (12)C19	2.3 (58)	2.9 (75)	66 (1679)
P36G31G	NA	60	0U FULL	IEC 60309 3P+E 9h 60A (IP44)	6	17.3	36	(24)C13 (12)C19	2.3 (58)	2.9 (75)	66 (1679)	
230/415 VAC, 3 PHASE	P36G16G	EMEA	32	0U FULL - Wide	IEC 60309 3P+N+E 6h 32A (IP44)	6	22	36	(24)C13 (12)C19	3.3 (85)	2.1 (53)	69 (1750)
	P48G04G	NA	30	0U FULL - Wide +	NEMA L22-30P	6	17.3	48	(48)C13	3.3 (85)	2.1 (53)	69 (1750)
	P24G08G	EMEA	32	0U FULL	IEC 60309 3P+N+E 6h 32A (IP44)	6	22	24	(12)C13 (12)C19	2 (52)	2.1 (53)	69 (1750)
	P36G15G	EMEA	16	0U FULL	IEC 60309 3P+N+E 6h 16A (IP44)	0	11	36	(30)C13 (6)C19	2 (52)	2.1 (53)	69 (1750)
	P36G33G	NA/EMEA	30/32	0U FULL	IEC 60309 3P+N+E 6h 30A/32A (IP44)	6	17.3/22.0	36	(24)C13 (12)C19	2.3 (58)	2.9 (75)	66 (1679)
	P48G30G	NA/EMEA	30/32	0U FULL	IEC 60309 3P+N+E 6h 30A/32A (IP44)	6	17.3/22.0	48	(24)C13/15/C19/C21 (24)C13/C15	2.2 (56)	3 (75)	70 (1780)
	P48G33G	NA/EMEA	20/16	0U MID	IEC 60309 3P+N+E 6h 20A/16A (IP44)	0	11.5/11.0	48	(24)C13/15/C19/C21 (24)C13/C15	2.2 (56)	3 (75)	70 (1780)
	P42G21G	NA/EMEA	60/63	0U FULL	IEC 60309 3P+N+E 6h 60A/63A (IP44)	12	34.5/44.4	42	(21)C13/15/C19/C21 (21)C13/C15	2.2 (56)	3 (75)	70 (1780)
P36G32G	NA/EMEA	20/16	0U FULL	IEC 60309 3P+N+E 6h 20A/16A (IP44)	3	11.5/11.0	36	(24)C13 (12)C19	2.3 (58)	2.9 (75)	66 (1679)	

G6 Intelligent Power Distribution Unit (iPDU) **USGv6 Certified**



For more information
and support, visit
www.panduit.com/pdu

WORLDWIDE SUBSIDIARIES AND SALES OFFICES

PANDUIT US/CANADA
Phone: 800.777.3300

PANDUIT EUROPE LTD.
London, UK
Phone: 44.20.8601.7200

PANDUIT SINGAPORE PTE. LTD.
Republic of Singapore
Phone: 65.6305.7575

PANDUIT JAPAN
Tokyo, Japan
Phone: 81.3.6863.6000

PANDUIT LATIN AMERICA
Guadalajara, Mexico
Phone: 52.33.3777.6000

PANDUIT AUSTRALIA PTY. LTD.
Victoria, Australia
Phone: 61.3.9794.9020

For a copy of Panduit product warranties, log on to www.panduit.com/warranty



For more information
Visit us at www.panduit.com
Contact Customer Service by email: cs@panduit.com
or by phone: 800.777.3300

© 2024 Panduit Corp.
ALL RIGHTS RESERVED.
PUSP97-WW-ENG
7/2024