

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	WEIGHT
P42D20M-XXYZ	SEE SHEET 2

**SPECIFICATION:**

**1. STANDARD:**

UNIT TYPE:	MONITORED INPUT
ORIENTATION:	VERTICAL, 0U
OUTLET QTY&TYPE:	(21)C13/C15, (21)C13/C15/C19
INPUT VOLTAGE:	200-240VAC
INPUT CURRENT:	60A (48A DERATED)
BREAKER QTY&TYPE:	(6)20AMP, DOUBLE-POLE
INPUT PHASE:	THREE-PHASE, DELTA
RATED POWER:	17.3 KVA
INPUT PLUG:	IEC 60309 3P+E 9H 60A (IP44)
INPUT POWER CORD:	SEE SHEET 2 PART NUMBER TABLE
REGULATORY STANDARD:	RoHS COMPLIANT

**2. ADDITIONAL:**

NONE

**3. ACCESSORIES:**






(1) QUICK-START GUIDE

**NOTES:**

1. PRIMARY DIMENSIONS ARE IN MILLIMETERS. SECONDARY DIMENSION ARE IN [ INCHES ] .
2. INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE, AND LOCAL CODES .
3. VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART .
4. FOR FULL PRODUCT FUNCTIONALITY REFER TO USER MANUAL .
5. DRAWING VIEWS SHOW THE INPUT CORD IN THE "TOP END FED" CONFIGURATION

**IDENTIFICATION**

FOR FINISHED GOOD PART NUMBER & DESCRIPTION TABLE SEE SHEET 2 CONFIGURABLE PART NUMBERS: **P42D20M-XX Y Z**




XX: FINISHED GOOD COLOR BL=BLACK YL=YELLOW RD=RED BU=BLUE WH=WHITE GN=GREEN	Y: INPUT FEED TYPE 1=TOP-END FED 2=BOTTOM-END FED	Z: INPUT CORD LENGTH A=1 METER B=2 METER C=3 METER
--	---	---


**PLUG/RECEPTACLE BLOCK**



**PLUG**  
IEC 60309, 3P 4W, 9H  
IP44 (SPLASHPROOF)  
60A, 250V, 3-PHASE MAX RATED INPUT  
48A DERATED



**RECEPTACLES**  
C13/C15 COMBO  
10A, 250V MAX RATED OUTPUT



**RECEPTACLES**  
C13/C15/C19 COMBO  
16A, 250V MAX RATED OUTPUT

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
01A	12/12/2022	Leo Liu	CSH	MJD	INITIAL RELEASE	P42D20M-XXYZ

WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGN THE CLIENT SIGNATURE BOX. THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY.		SIGN
		DATE
		PRINT
TITLE <b>INTELLIGENT SERIES PDU</b> <b>P42D20M-XXYZ</b> CUSTOMER DRAWING		
ITEM REVISION NAME:		<b>PANDUIT</b>
DATASHEET FILE NAME:		
UNLESS OTHERWISE SPECIFIED DIMENSIONAL TOLERANCE ARE: mm [IN]		MATERIAL/COLOR: <b>N/A</b>
Tolerance(mm) 0.4<50 ±0.5 50.4<250 ±1.0 250.4<500 ±1.5 500.4<1000 ±2.5 1000.4<2000 ±4.0		DRAWING NUMBER: <b>P42D20M-XXYZ_DC</b>
THIRD ANGLE PROJECTION	SCALE <b>NONE</b>	SCALE <b>B</b>
DRAWN BY Leo	DATE 12/12/2022	SHT 1 OF 2



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

FINISHED GOOD PART NUMBER	FINISHED GOOD DESCRIPTION	COLOR	INPUT CORD LENGTH	WEIGHT
P42D20M	VERTICAL,(21)C13/C15, (21)C13/C15/C19, MONITORED INPUT, 200-240VAC/60A (48A DERATED) / 3 PHASE, TOP-END FED, 3 METER INPUT CORD, BLACK	BLACK (RAL 9005)	3M(+254mm/-127mm) 10'(+10"/-5")	6.8kg

B

B



A

A

WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGN THE CLIENT SIGNATURE BOX. THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY.		SIGN																			
		DATE																			
		PRINT																			
TITLE INTELLIGENT SERIES PDU P42D20M-XYZ CUSTOMER DRAWING																					
ITEM REVISION NAME:																					
DATASHEET FILE NAME:																					
UNLESS OTHERWISE SPECIFIED DIMENSIONAL TOLERANCE ARE: mm [IN]			MATERIAL/COLOR:																		
<table border="0"> <tr> <td></td> <td>Tolerance(mm)</td> <td></td> </tr> <tr> <td>0&lt;L&lt;50</td> <td>±0.5</td> <td></td> </tr> <tr> <td>50&lt;L&lt;250</td> <td>±1.0</td> <td></td> </tr> <tr> <td>250&lt;L&lt;500</td> <td>±1.5</td> <td></td> </tr> <tr> <td>500&lt;L&lt;1000</td> <td>±2.5</td> <td></td> </tr> <tr> <td>1000&lt;L&lt;2000</td> <td>±4.0</td> <td></td> </tr> </table>				Tolerance(mm)		0<L<50	±0.5		50<L<250	±1.0		250<L<500	±1.5		500<L<1000	±2.5		1000<L<2000	±4.0		N/A
	Tolerance(mm)																				
0<L<50	±0.5																				
50<L<250	±1.0																				
250<L<500	±1.5																				
500<L<1000	±2.5																				
1000<L<2000	±4.0																				
THIRD ANGLE PROJECTION			DRAWING NUMBER: P42D20M-XYZ_DC																		
DRAWN BY	DATE	CHK	SCALE																		
Leo	12/12/2022	Hanson	NONE																		
SHT 2 OF 2			SCALE B																		

01A	12/30/2022	Leo Liu	CSH	MJD	INITIAL RELEASE	P42D20M-XYZ			
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN			

