




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.




**LEFT VIEW**




**REAR VIEW**



**RIGHT VIEW**



**FRONT VIEW**



**BOTTOM VIEW**

**SPECIFICATION:**

- 1. STANDARD
  - UNIT TYPE: MONITORED INPUT
  - ORIENTATION: VERTICAL, 0U
  - OUTLET QTY & TYPE: (24)C13, (12)C19
  - INPUT VOLTAGE: 200-240VAC
  - INPUT CURRENT: 60A (48A DERATED)
  - BREAKER QTY & TYPE: (6) 20A, DOUBLE-POLE
  - INPUT PHASE: THREE-PHASE (DELTA)
  - RATED POWER: 17.3 kVA
  - INPUT PLUG: SEE TABLE SHEET 2
  - INPUT POWER CORD: SEE TABLE SHEET 2
  - REGULATORY STANDARD: RoHS COMPLIANT
- 2. ADDITIONAL:
  - OUTLET CONTROL RELAY: NORMALLY OPEN 80 AMP INRUSH
- 3. ACCESSORIES:
  - (1) QUICK-START GUIDE

**NOTES:**


1. PRIMARY DIMENSIONS ARE IN MILLIMETERS. SECONDARY DIMENSIONS ARE IN [INCHES]
2. INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE, AND LOCAL CODES
3. VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PRODUCT
4. FOR FULL PRODUCT FUNCTIONALITY REFER TO USER MANUAL
5. DRAWING VIEWS SHOW THE INPUT CORD IN THE "TOP END FED" CONFIGURATION

**IDENTIFICATION**

FOR FINISHED GOOD PART NUMBER & DESCRIPTION TABLE SEE SHEET 2 CONFIGURABLE PART NUMBERS: P36D31M-XXYZ

|   |   |  |
|---|---|--|
| XX: FINISHED GOOD COLOR<br>BL = BLACK YL =YELLOW<br>RD =RED BU =BLUE<br>WH =WHITE GN =GREEN | Y: INPUT FEED TYPE<br>1 =TOP-END FED<br>2 =BOTTOM-END FED | Z: INPUT CORD LENGTH<br>A =1 METER<br>B =2 METER<br>C =3 METER |
|---|---|--|

**PLUG / RECEPTACLE BLOCK**



**PLUG**  
IEC 60309, 3P 4W, 9H  
IP44 (SPASHPROOF)  
60A, 250VAC MAX RATED INPUT  
(48A DERATED)



**RECEPTACLE**  
IEC 60320 C13  
10A, 250V MAX RATED OUTPUT



**RECEPTACLE**  
IEC 60320 C19  
16A, 250V MAX RATED OUTPUT

| REV.      | DATE       | BY  | CHK  | APR | DESCRIPTION                              | ECN     |
|-----------|------------|-----|------|-----|--|---------|
| 03A       | 02/23/2022 | WAC | PJST | MJD | CORRECTED DEPTH DIM FROM 75MM TO 80MM    | P36D31M |
| 02A       | 11/2/2021  | WAC | PJST | MJD | REVISED 3D MODEL LAYOUT AND OUTLET TYPES | P36D31M |
| 01A       | 10/13/2021 | WAC | PJST | MJD | INITIAL DC RELEASE                       | P36D31M |
| REVISIONS |            |     |      |     |  |         |

WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGN THE CLIENT SIGNATURE BOX. THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY.

SIGN \_\_\_\_\_ DATE \_\_\_\_\_ PRINT \_\_\_\_\_

TITLE: INTELLIGENT SERIES PDU  
**P36D31M-XXYZ**  
CUSTOMER DRAWING

ITEM REVISION NAME: \_\_\_\_\_ DATASET FILE NAME: \_\_\_\_\_

UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: m m [IN]

| Tolerance (mm) |      |
|----------------|------|
| 0<L≤50         | ±0.5 |
| 50<L≤250       | ±1.0 |
| 250<L≤500      | ±1.5 |
| 500<L≤1000     | ±2.5 |
| 1000<L≤2000    | ±4.0 |

THRID ANGLE PROJECTION

MATERIAL: N/A

DRAWING NUMBER: **P36D31M\_DC**

|         |                  |        |            |              |         |
|---------|------------------|--------|------------|--------------|---------|
| BY: WAC | DATE: 10/13/2021 | CHK: - | SCALE: NTS | SHEET 1 OF 2 | SIZE: B |
|---------|------------------|--------|------------|--------------|---------|



| FINISHED GOOD PART NUMBER | FINISHED GOOD DESCRIPTION   | COLOR        | INPUT CORD LENGTH                    | WEIGHT |
|---------------------------|---|--------------|--------------------------------------|--------|
| P36D31M                   | MI PDU, 60AMP, (24)C13, (12)C19, IEC 60309 3P+E 9H-3M, TOP FED, BLACK | BLACK (9005) | 3M (+254MM / -127MM) [10'(+10"/-5")] | 10.2kg |

B

B

A

A

| REV.      | DATE       | BY  | CHK  | APR | DESCRIPTION                              | ECN     |
|-----------|------------|-----|------|-----|--|---------|
| 03A       | 02/23/2022 | WAC | PJST | MJD | CORRECTED DEPTH DIM FROM 75MM TO 80MM    | P36D31M |
| 02A       | 11/2/2021  | WAC | PJST | MJD | REVISED 3D MODEL LAYOUT AND OUTLET TYPES | P36D31M |
| 01A       | 10/13/2021 | WAC | PJST | MJD | INITIAL DC RELEASE                       | P36D31M |
| REVISIONS |            |     |      |     |  |         |

WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGN THE CLIENT SIGNATURE BOX. THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY.

SIGN \_\_\_\_\_  
DATE \_\_\_\_\_  
PRINT \_\_\_\_\_

TITLE  
**INTELLIGENT SERIES PDU**  
**P36D31M-XXYZ**  
CUSTOMER DRAWING

ITEM REVISION NAME \_\_\_\_\_  
DATASET FILE NAME \_\_\_\_\_

UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: m m [IN]

| Tolerance (mm) |      |
|----------------|------|
| 0<L≤50         | ±0.5 |
| 50<L≤250       | ±1.0 |
| 250<L≤500      | ±1.5 |
| 500<L≤1000     | ±2.5 |
| 1000<L≤2000    | ±4.0 |

THRID ANGLE PROJECTION

MATERIAL: **N/A**

DRAWING NUMBER: **P36D31M\_DC**

BY: WAC DATE: 10/13/2021 CHK: - SCALE: NTS SHEET 2 OF 2 SIZE: B