
THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NO.	PKG.QTY.	CTN.QTY.	TAPE MATERIAL	"W" (WIDTH)	"T" (THICKNESS)	ROLL LENGTH	
META-X	10 ROLLS			.495"±.010" [12.6±.25]	.006"±.0005" [.15±.01]	16 ft. 4.88 meters	
METS4-X	10 ROLLS	40 ROLLS	304 GRADE Stainless steel	.495"±.010" [12.6±.25]	.005"±.0005 [.12±.01]	21 ft. 6.4 meters	
METS3-X	10 ROLLS	40 ROLLS	316 GRADE Stainless steel	.495"±.010" [12.6±.25]	.005"±.0005 [.12±.01]	21 ft. 6.4 meters	



 $\mathsf{B}$ 

## NOTE:

- 1. TAPE USED WITH PANDUIT EMBOSSING TOOL PART NO.MEHT.
- 2. BRACKETS [ ] DENOTES DIMENSION IN MILLIMETERS.

2					1									
	REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	JAMB	12/04	EJD	4:1	SHT 1 0F 1	SIZE	
	00A	12/04	JMMR	EJD	JJB	DRAWING RELEASE.	12339	E			IRD ANGLE OJECTION	DRAWING NUMBER: N41206BS.		
	01A	6/06	MIM	DKB	JJB	REVISED WIDTH DIMENSION	SS00189		.1 [2.54]	.XXX ±	_			
	02	11/16/18	RVU	ANR0	JHAC	ADDED 45° CHAMFERS ON BOTH SIDES OF TAPE.	GAECN04726	UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]				MATERIAL:		
								N41206BS/03  DATASET FILE NAME N41206BS_DC/03B			PANDU			
								CUSTOMER DRA						
										WING	4	<u> </u>		
Α								ACCE	SSORY TA	ANDUIT EMBOSSING	G TOOL	Λ		
								TITLE						