

# DP4300H and DP4600H Thermal Transfer Desktop Printers

The DP4300H and DP4600H Thermal Transfer Desktop Printers produce high-quality print-on-demand labels for a wide range of applications for electrical and network infrastructure. These high-volume printers are ideal for OEM, MRO, Construction, Data Center, and Enterprise labeling.



Quickly create self-laminating labels, heat shrink labels, and marker plates for wire and cable marking. Easily print raised panel labels, electrical component labels, network component labels, arc flash labels, and safety signs for equipment and facility identification.

With very fast printing speed, rugged design, color touchscreen display, wide variety of label and ribbon options, and Easy-Mark Plus™ Labeling Software included, the DP4300H and DP4600H are ideal for any high-volume label printing needs.

## KEY FEATURES AND BENEFITS

<b>High volume printing:</b>	Rugged, durable design for printing in all environments
<b>Fast label production:</b>	Up to 11.8 inches per second print speed
<b>Up to 600 dots per inch (dpi) print resolution:</b>	Superior print quality for all type of labels
<b>Large color touchscreen display:</b>	Easy to use screen with intuitive interface
<b>Quick and easy loading of label and ribbon media:</b>	Minimize setup time to switch label and ribbon rolls, maximize uptime
<b>Easy-Mark Plus™ Labeling Software included with printer:</b>	No additional investment for labeling software, print right out of the box
<b>USB, ethernet, and serial connectivity:</b>	Increased flexibility to quickly connect to any computer

## TECHNICAL PERFORMANCE INFORMATION

	DP4300H	DP4600H
<b>Print method :</b>	300 dpi thermal transfer	600 dpi thermal transfer
<b>Print speed (maximum) :</b>	11.8" (300mm) per second	5.9" (150mm) per second
<b>Maximum print width:</b>	4.16" (105.7mm)	
<b>Maximum print length:</b>	78.74" (2.0m)	39.37" (1.0m)
<b>Weight:</b>	22 lbs. (10 kg)	
<b>Size (width x height x depth):</b>	9.9" x 11.3" x 18.1" (252mm x 288mm x 460mm)	
<b>Connectivity:</b>	USB, Ethernet, Serial	
<b>Regulatory Compliance:</b>	FCC, cUL, ICES3, CE, UKCA, CB, CCC, KC, BSMI, RCM, ECAS, CoC	
<b>Compatibility:</b>	Windows 10, 11^	

^Windows is a registered trademark of Microsoft Corp. in the United States and/or other countries.

## ORDERING INFORMATION

Part Number	Part Description	Std. Pkg. Qty.
DP4300H	300 dpi printer; includes printer, Panduit Easy-Mark Plus™ Labeling Software, RHEH4BL black hybrid ribbon, USB cable, quick start guide, and U.S. power cord; for use in North America.	1
DP4600H	600 dpi printer; includes printer, Panduit Easy-Mark Plus™ Labeling Software, RHEH4BL black hybrid ribbon, USB cable, quick start guide, and U.S. power cord; for use in North America.	

# Thermal Transfer Desktop Printers

## DP4300HD Two-Sided Thermal Transfer Desktop Printer

The DP4300HD Two-Sided Thermal Transfer Desktop Printer enables printing on both sides of two-side printable labels at the same time. This functionality saves 50% of the time required to print on both sides compared to using a single-sided printer.

The DP4300HD printer produces high-quality print-on-demand labels for wire and cable marking applications using Panduit Two-Sided Heat Shrink Labels. This solution is ideal for labeling in OEM, MRO, and Construction. With the included Panduit Easy-Mark Plus™ Labeling Software, designing and printing labels is quick and easy.

Panduit offers a wide range of compatible labeling options, including Military Grade Two-Sided Heat Shrink Labels, Halogen-Free Two-Sided Heat Shrink Labels, and continuous heat shrink label material.



### KEY FEATURES AND BENEFITS

<b>Rugged, durable design:</b>	Ideal printer for high volume labeling applications, industrial production, and harsh environments
<b>Print two-sided heat shrink labels in one pass:</b>	Maximize printing efficiency, cut printing time for two-sided labels by 50%
<b>300 dots per inch (dpi) print resolution:</b>	Provides crisp, clear, legible print for best label appearance
<b>Large color touchscreen display:</b>	Easy to use screen with intuitive interface
<b>Quick and easy loading of label and ribbon media:</b>	Minimize setup time to switch label and ribbon rolls, maximize uptime
<b>Easy-Mark Plus™ labeling software included with printer:</b>	No additional investment for labeling software, print right out of the box
<b>USB, ethernet, and serial connectivity:</b>	Increased flexibility to quickly connect to any computer

### TECHNICAL PERFORMANCE INFORMATION

<b>Print method:</b>	300 dpi thermal transfer
<b>Print speed (maximum) :</b>	5.9" (150mm) per second
<b>Maximum print width:</b>	4.16" (105.7mm)
<b>Label types:</b>	Military Grade Two-Sided Heat Shrink, Halogen Free Two-Sided Heat Shrink, Continuous Heat Shrink
<b>Weight:</b>	46 lbs. (21 kg)
<b>Size (width x height x depth):</b>	9.8" x 15.6" x 23.4" (248mm x 395mm x 594mm)
<b>Connectivity:</b>	USB, Ethernet, Serial
<b>Regulatory compliance:</b>	FCC, cUL, ICES3, CE, UKCA, CB
<b>Compatibility:</b>	Windows 10, 11 <sup>^</sup>

<sup>^</sup>Windows is a registered trademark of Microsoft Corporation in the United States and/or other countries

### ORDERING INFORMATION

Part Number	Part Description	Std. Pkg. Qty.
DP4300HD	300 dpi printer; includes printer, Panduit Easy-Mark Plus Labeling Software, 2 rolls of RHEH4BL black hybrid ribbon, USB cable, quick start guide, and U.S. power cord; for use in North America.	1

For more information visit:  
[www.panduit.com](http://www.panduit.com)

# Thermal Transfer Desktop Printers



## THERMAL TRANSFER RIBBONS

Part Number	Part Description	Width In. (mm)	Length ft (m)	Std. Pkg. Qty.
RHEH4BL	Black hybrid thermal transfer ribbon. Use with heat shrink, self-laminating, Turn-Tell®, and vinyl cloth.	4.33 (110.0)	1181.0 (363.0)	1
RHER4BL	Black resin thermal transfer ribbon. Use with polyester labels, continuous vinyl tape, marker plates, and raised panel labels.			
RHER4WH	White resin thermal transfer ribbon. Use with polyester labels, continuous vinyl tape, marker plates, and raised panel labels.	4.50 (114.3)		
RHER4BL-A	Black resin thermal transfer ribbon. Use with high-temperature marker plates.	4.33 (110.0)		
RHER4BL-C	Black resin thermal transfer ribbon. Use with fluid resistant heat shrink markers and white polyimide labels.			
RHER4BL-E	Black resin thermal transfer ribbon. Use with standard marker plates and component labels for extra durability for harsh environments.			

## DESKTOP PRINTER ACCESSORIES

Part Number	Part Description
DP4X00H-CUT	Optional power/automatic cutter for DP4300H, DP4600H, and DP4300HD thermal transfer desktop printers.
DP4X00H-PCUT	Optional power/automatic perforation cutter for DP4300H, DP4600H, and DP4300HD thermal transfer desktop printers.
TDP43ME-RS	External label roll stand for use with continuous tapes
PTR-CLN	Printer cleaning kit—contains (1) cleaning pen, (8) cleaning solution soaked wipes, (8) foam swabs pre-saturated with cleaning solution.

## DESKTOP LABELING APPLICATIONS

					
Wire and Cable Marking	Terminal Block Labeling	Electrical Infrastructure Labeling	Marker Plates	Raised Panel Labels	Network Infrastructure Labeling
					
2-Sided Heat Shrink Labels	Pipe Marking	Turn-Tell® Labels	Safety Signs	Electrical Hazard Labels	Flag Labels

## RELATED PRODUCTS




TDP43ME



PXE™ Mobile Printers



Abrasion Protection



Wiring Duct

### WORLDWIDE SUBSIDIARIES AND SALES OFFICES

PANDUIT US/CANADA  
Phone: 800.777.3300

PANDUIT EUROPE LTD.  
London, UK  
Phone: 44.20.8601.7200

PANDUIT SINGAPORE PTE. LTD.  
Republic of Singapore  
Phone: 65.6305.7575

PANDUIT JAPAN  
Tokyo, Japan  
Phone: 81.3.6863.6000

PANDUIT LATIN AMERICA  
Guadalajara, Mexico  
Phone: 52.33.3777.6000

PANDUIT AUSTRALIA PTY. LTD.  
Victoria, Australia  
Phone: 61.3.9794.9020

For a copy of Panduit product warranties, log on to [www.panduit.com/warranty](http://www.panduit.com/warranty)

For more information  
Visit us at [www.panduit.com](http://www.panduit.com)  
Contact Customer Service by email: [cs@panduit.com](mailto:cs@panduit.com)  
or by phone: 800.777.3300

© 2024 Panduit Corp.  
ALL RIGHTS RESERVED.  
IDCB99-SA-ENG  
10/2024